

# Electronic housing - EMG 30-LG/SET - 2940016

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Electronic housing set, consisting of electronic housing and printed circuit termination blocks, pitch 5

## Product Features

- Choice of four cover sizes in transparent or color versions
- Practical and easy-to-wire conductor connections
- High degree of flexibility due to the wide choice of versions
- User-friendly and safe mounting on DIN rails according to EN 60715
- Uniform and appropriate housing technology
- Space-saving accommodation of electronic components in finely graded module versions available with 10 to 150 mm pitch
- Inflammability class V0 insulation material (according to UL 94)
- Shock and contamination-proof accommodation of electronic components
- Universal PCBs for all pitches

## Key commercial data

|                         |               |
|-------------------------|---------------|
| <b>package_quantity</b> | 5             |
| <b>GTIN</b>             | 4017918079796 |

## Technical data

### General

|                         |                                |
|-------------------------|--------------------------------|
| <b>Housing type</b>     | Component housing              |
| <b>Housing material</b> | Polycarbonate fiber reinforced |
| <b>Color</b>            | green                          |

### Ambient conditions

|  |                   |
|--|-------------------|
| <b>Ambient temperature (operation)</b> | -40 °C ... 125 °C |
|--|-------------------|

### Dimensions

|                              |         |
|------------------------------|---------|
| <b>Length</b>                | 75 mm   |
| <b>Constructional height</b> | 47.5 mm |
| <b>Width</b>                 | 30 mm   |
| <b>Pitch</b>                 | 5 mm    |

### Technical data

|  |                    |
|--|--------------------|
| <b>Inflammability class according to UL 94</b>                       | V0                 |
| <b>Power dissipation at 20°C in the horizontal mounting position</b> | 1.5 W 1.7 W 7.5 mm |

# Electronic housing - EMG 30-LG/SET - 2940016

## Technical data

### Technical data

|   |                   |
|---|-------------------|
| Power dissipation at 20°C in the horizontal mounting position | 1.7 W 1.9 W 15 mm |
| Power dissipation at 20°C in the horizontal mounting position | 3.6 W 4.9 W 52 mm |
| Number of positions   | 10                |

## classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27180401 |
| eCl@ss 4.1 | 27180401 |
| eCl@ss 5.0 | 27180506 |
| eCl@ss 5.1 | 27180506 |
| eCl@ss 6.0 | 27180802 |
| eCl@ss 7.0 | 27182702 |
| eCl@ss 8.0 | 27182702 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001031 |
| ETIM 3.0 | EC001031 |
| ETIM 4.0 | EC001031 |
| ETIM 5.0 | EC000886 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31261501 |
| UNSPSC 7.0901 | 31261501 |
| UNSPSC 11     | 31261501 |
| UNSPSC 12.01  | 31261501 |
| UNSPSC 13.2   | 31261501 |

## approvals

GOST /

### Approval details



## accessories

### Filler plug

## Electronic housing - EMG 30-LG/SET - 2940016

### accessories

EMG-KA - 2941510



---

### Device marking

EMG-GKS 22 - 2941594



---

### PCB

P 1-EMG 30 - 2947912



---

### accessories

EMG-GKS 12 - 2947035




EMG-SGKS 10 - 2947585



# Electronic housing - EMG 30-LG/SET - 2940016

## Drawings


Dimensioned drawing



1 = Top edge of the PCB B = Housing width

# Electronic housing - EMG 30-LG/SET - 2940016

Dimensioned drawing



Pitch 5 mm = Area for mounting components, 38 mm in the hood =  
Area for mounting components, 45 mm in the housing

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>