

# Components of electronic housing - ME MAX 67,5 3-3 KMGY - 2200526

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



## Product Features

- Plug-in connection with screw, spring-cage or fast connection technology
- DIN rail bus connector as an option
- Labels for additional labeling as an option
- Large PCB surface despite compact housing dimensions
- Large front surface for high-pos. plugs or operating and setting elements
- The fitted cover is easy to adapt and print
- Easy module replacement without interrupting the contact chain
- Functional earth ground contact as an option
- Fixed or plug-in connection technology can be combined on up to three connection levels, with different pitches
- Transparent front cover can be swiveled

## Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4046356606028

## Technical data

### General

<b>Housing type</b>	Complete housing
<b>Housing material</b>	Polyamide
<b>Color</b>	light gray

### Ambient conditions

<b>Ambient temperature (operation)</b>	-40 °C ... 105 °C
--	-------------------

### Dimensions

<b>Length</b>	99 mm
<b>Constructional height</b>	114.5 mm
<b>Width</b>	67.5 mm

### Technical data

<b>Inflammability class according to UL 94</b>	V0
--	----

# Components of electronic housing - ME MAX 67,5 3-3 KMGY - 2200526

## Technical data

### Technical data

<b>Power dissipation at 20°C in the horizontal mounting position</b>	9.1 W 17.5 W
--	--------------

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27180401
<b>eCl@ss 4.1</b>	27180401
<b>eCl@ss 5.0</b>	27180506
<b>eCl@ss 5.1</b>	27180506
<b>eCl@ss 6.0</b>	27180802
<b>eCl@ss 7.0</b>	27182702
<b>eCl@ss 8.0</b>	27182702

### ETIM

<b>ETIM 3.0</b>	EC001031
<b>ETIM 4.0</b>	EC001031
<b>ETIM 5.0</b>	EC001031

### UNSPSC

<b>UNSPSC 6.01</b>	31261501
<b>UNSPSC 7.0901</b>	31261501
<b>UNSPSC 11</b>	31261501
<b>UNSPSC 12.01</b>	31261501
<b>UNSPSC 13.2</b>	31261501

## Drawings