

# Electronic housing - ME MAX 6,2 SC-TBUS 4-4 KMGY - 2869634

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Extra slim electronic housing for DIN rail bus connector, pitch 6.2 mm, 4 connection levels, 8-pos. with screw connection

## Product Features

- Housing can be labeled using standard laser systems
- Easy device testing thanks to integrated test openings
- IP20 shock protection
- Same PCB geometry for spring-cage and screw versions
- Transparent front cover can be swiveled, reversed, and labeled

## Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4017918975135

## Technical data

### Dimensions

<b>Length</b>	93.1 mm
<b>Width</b>	6.2 mm
<b>Pitch</b>	6.2 mm

### General

<b>Range of articles</b>	ME MAX 6,2 SC TBUS
<b>Inflammability class according to UL 94</b>	V0
<b>Number of positions</b>	8

### Connection data

<b>Conductor cross section solid min.</b>	0.2 mm <sup>2</sup>
<b>Conductor cross section solid max.</b>	2.5 mm <sup>2</sup>
<b>Conductor cross section stranded min.</b>	0.2 mm <sup>2</sup>
<b>Conductor cross section stranded max.</b>	2.5 mm <sup>2</sup>
<b>Conductor cross section AWG/kcmil min.</b>	26
<b>Conductor cross section AWG/kcmil max</b>	12

## classifications

eCl@ss

# Electronic housing - ME MAX 6,2 SC-TBUS 4-4 KMGY - 2869634

## classifications

### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## approvals

UL Recognized / cUL Recognized / cULus Recognized /

### Approval details

UL Recognized
---------------

cUL Recognized		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	8 A	8 A
mm <sup>2</sup> /AWG/kcmil	30-12	30-12

cULus Recognized
------------------

## Electronic housing - ME MAX 6,2 SC-TBUS 4-4 KMGY - 2869634

accessories

### Screwdriver tools

SZF 1-0,6X3,5 - 1204517



---

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>