


# C1206C104K5RACTU

aka C1206C104K5RAC7800

Capacitor, ceramic, 0.1 uF, +/-10% Tol, 50V, X7R, 1206



## Dimensions (mm)

ID	Dimension	Tolerance
L	3.20	+/-0.20
W	1.60	+/-0.20
T	0.78	+/-0.1
B	0.50	+/-0.25

## Specifications

<b>Manufacturer:</b>	KEMET
<b>Capacitance:</b>	0.1 uF
<b>Chip Size:</b>	1206
<b>Voltage:</b>	50V
<b>Temperature Coefficient:</b>	X7R
<b>Tolerance:</b>	+/-10%
<b>Application:</b>	Std Chip
<b>Termination Type:</b>	Tin
<b>Marked:</b>	No
<b>Dissipation Factor:</b>	2.5%
<b>Insulation Resistance:</b>	5 GOhm
<b>Dielectric Strength:</b>	125V
<b>Miscellaneous Electrical:</b>	Regarding Aging Rate: Capacitance measurements (including tolerance) are indexed to a referee time of 1000 hours
<b>Package Kind:</b>	T&R
<b>Package Size:</b>	7in
<b>Package Type:</b>	Plastic Tape
<b>Package Quantity:</b>	4000