

Components of electronic housing - UM-PRO 122 COVER-L BK - 2200158

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Lateral element (left) with mounting foot for DIN rails for 122 mm wide UM-PRO profiles

Product Features

- Plug-in assembly reduces assembly time and therefore saves costs
- Mounting close to the edge provides wiring advantages
- Freely positionable covers offer flexibility
- PE contacts that can be fitted on both sides ensure safety
- Additional foot elements increase mechanical stability
- Temperature range up to 100°C extends the possible fields of application (UM-PRO)
- Additional labeling of PCB with Phoenix Contact PMB module marker carrier (drill hole diameter 4 mm)
- Labeling area for standard SK strips or TML marking foil (max. height 6 mm)
- Device communication can be extended by BUS cross contacting
- Well-designed profile geometry increases the form stability

Key commercial data

package_quantity	10
GTIN	4046356547406

Technical data

General

Housing type	Side cover
Housing material	Polyamide
Color	black

classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27182003
eCl@ss 7.0	27182701

Components of electronic housing - UM-PRO 122 COVER-L BK - 2200158

classifications

eCl@ss

eCl@ss 8.0	27182701
------------	----------

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC000721
ETIM 5.0	EC000721


UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

approvals

UL Recognized /

Approval details



Drawings

Dimensioned drawing

