

# Electronic housing - HC-ALU 6-53,5 PROFILE 100 - 2200887

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Panel mounting base, Lower part, Color: aluminum, Width: 100 mm

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4046356715782

## Technical data

### General

<b>Housing type</b>	Panel mounting base
<b>Housing material</b>	Aluminum
<b>Color</b>	aluminum

### Ambient conditions

<b>Ambient temperature (operation)</b>	-40 °C ... 85 °C
--	------------------

### Dimensions

<b>Width</b>	100 mm
--------------	--------

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27180401
<b>eCl@ss 4.1</b>	27180401
<b>eCl@ss 5.0</b>	27180506
<b>eCl@ss 5.1</b>	27180506
<b>eCl@ss 6.0</b>	27182003
<b>eCl@ss 7.0</b>	27182701
<b>eCl@ss 8.0</b>	27182701

### ETIM

<b>ETIM 3.0</b>	EC001031
<b>ETIM 4.0</b>	EC000721
<b>ETIM 5.0</b>	EC000721

### UNSPSC

# Electronic housing - HC-ALU 6-53,5 PROFILE 100 - 2200887

classifications

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Drawings

Dimensioned drawing

