

Voltage tester - SF-VT VDE - 1212598

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Voltage tester, single-position, for 150 - 250 V, conforms to DIN 57680/6 and VDE 0680/6, can also be used as an actuation tool for spring-cage terminal blocks, size: 0.5 x 3.0 x 70 mm, VDE insulated, with non-slip grip

Product Features

- Shock-proof, dust-proof, and splash-proof housing, IP65
- DC and AC voltage tests in the range from 6 V to 400 V
- Polarity test (+/-) for DC voltage
- LED indicator

Key commercial data

package_quantity	10
GTIN	4046356590723

Technical data

Dimensions

Length (b)	140 mm
Blade thickness	0.5 mm
Blade width	3 mm
Blade height	65 mm

General

Design	Bladed
Test standard	ISO 57680/6 VDE 0680/6
Minimum voltage	150 V AC
Max. voltage	250 V AC

classifications

eCl@ss

eCl@ss 4.0	21040402
eCl@ss 4.1	21040402
eCl@ss 5.0	21040402
eCl@ss 5.1	21040402
eCl@ss 6.0	21040290
eCl@ss 7.0	21040290

Voltage tester - SF-VT VDE - 1212598

classifications

eCl@ss

eCl@ss 8.0	21040290
-------------------	----------

ETIM

ETIM 4.0	EC000494
ETIM 5.0	EC000494

UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

Drawings

Voltage tester - SF-VT VDE - 1212598

Pictogram

