

Stripping machine - WF 1000 - 1212149

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Stripping machine with integrated graphic display, for conductors and cables up to 6 mm in diameter, 230 V version

Product Features

- The clamping force automatically adjusts itself to the required extraction force
- Compact stripping machine for automatically stripping conductors with a cross section of 0.08 to 6 mm²
- Even special types of insulation, such as PTFE and silicone, can be stripped in addition to standard types
- Pressure points on sensitive insulation are avoided
- The stripping dimensions are set individually via knobs and are shown on the large display
- Multi-strand cables with a diameter of up to 6 mm can also be stripped
- Partial stripping is supported

Key commercial data

package_quantity	1
GTIN	4046356457026

Technical data

Dimensions

Length (b)	363 mm
Height	221 mm
Width (a)	141 mm
Diameter, conductor entry opening	6.00 mm

General

Compression	trapezoidal
Working cycle	0.3 s
Power consumption	160 VA
Maximum throughput	6
Min. cross section	0.08 mm ²
Max. cross section	6 mm ²
Minimum stripping length	3 mm
Maximum stripping length	20 mm
Partial stripping length range minimum	2 mm
Partial stripping length range maximum	20 mm

Stripping machine - WF 1000 - 1212149

classifications

eCl@ss

eCl@ss 4.0	21040302
eCl@ss 4.1	21040302
eCl@ss 5.0	21040302
eCl@ss 5.1	21040302
eCl@ss 6.0	21043706
eCl@ss 7.0	21043706
eCl@ss 8.0	21043706

ETIM

ETIM 2.0	EC000142
ETIM 3.0	EC000142
ETIM 4.0	EC000163
ETIM 5.0	EC002778

UNSPSC

UNSPSC 6.01	23171604
UNSPSC 7.0901	23171604
UNSPSC 11	23171604
UNSPSC 12.01	23171604
UNSPSC 13.2	23171604

approvals

GOST /

Approval details



accessories

Knife

WF 1000/SB - 1212279



Drawings



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>