


# DS Radial Type, Standard Series

- ▶ Endurance : 2.5V 70°C 1000 hours, 2.7V 60°C 1000 hours
- ▶ The small size and high capacitance, low resistance
- ▶ Can be charge and discharge more times than secondary batteries



Item	Characteristics	
Operating temperature range	-25 ~ +70°C	-40 ~ +60°C
Rated Working Voltage	2.5VDC	2.7VDC
Capacitance tolerance	-20 ~ +80% at 20°C	
Low temperature characteristics	Capacitance change Internal resistance	Within ±30% of initial value at +20°C (-25 to +70°C, -40 to +60°C) Less than 400% of initial at +20°C
Endurance (2.5V 70°C 1000h, 2.7V 60°C 1000h)	Test time Capacitance change Internal resistance	1000 hours Within ±30% of initial value Less than 300% of initial at specified value
Shelf life (2.5V 70°C 1000h, 2.7V 60°C 1000h)	After 1000 hours no load test same as endurance	

## ● DRAWING



Unit : mm

φD	8	10	16	18	22
P	3.5	5	7.5	7.5	1.0
φd	0.6	0.6	0.8	0.8	1.0
β	1.5			2.0	

## ● CHARACTERISTIC LIST & DIMENSIONS

Rate Working Voltage	Capacitance (F)	Internal resistance (mΩ) at 1kHz	Leakage Current (mA Max.) after 30 minutes	Size Ø D × L (mm)
2.5	3	140	2.4	8×20
	5	110	4	10×20
	10	65	8	10×30
	25	35	20	16×25
	60	20	48	18×40
2.7	3	60	2.4	8×20
	5	50	4	10×20
	10	35	8	10×30
	25	20	20	16×25
	50	15	48	18×40