

Fax: 0049-(0)7223-284-245



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 14.08.2017 Version number 11 Revision: 14.08.2017

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- · 1.1 Product identifier
- · Trade name: UHU Sekundenkleber CA 202 20 g
- 1.2 Relevant identified uses of the substance or mixture and uses advised against

No further relevant information available.

- · Application of the substance / the mixture Adhesives
- · 1.3 Details of the supplier of the safety data sheet
- Manufacturer/Supplier:

UHU GmbH & Co.KG

Herrmannstraße 7

D-77815 Bühl (Baden)

Tel.:0049-(0)7223-284-0

email: info@uhu.boltongroup.de

· Further information obtainable from: UHU QESH

· 1.4 Emergency telephone number:

Tel.: + 49 (0) 30/19240 (Notruf) Tel.: + 49 (0) 72 23/28 40

SECTION 2: Hazards identification

- · 2.1 Classification of the substance or mixture
- Classification according to Regulation (EC) No 1272/2008

The product is not classified according to the CLP regulation.

- · 2.2 Label elements
- · Labelling according to Regulation (EC) No 1272/2008 Void
- · Hazard pictograms Void
- · Signal word Void
- · Hazard statements Void
- · Additional information:

Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

- · 2.3 Other hazards
- · Results of PBT and vPvB assessment
- · **PBT:** Not applicable.
- · **vPvB**: Not applicable.

SECTION 3: Composition/information on ingredients

- · 3.2 Mixtures
- · Description: Adhesive
- · Dangerous components: Void
- · Additional information: For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- · 4.1 Description of first aid measures
- General information: No special measures required.
- · After inhalation: No special measures required.

(Contd. on page 2)





Printing date 14.08.2017 Version number 11 Revision: 14.08.2017

Trade name: UHU Sekundenkleber CA 202 20 g

(Contd. of page 1)

· After skin contact:

Rinse with warm water.

Do not pull solidified product off the skin.

- · After eye contact: Rinse opened eye for several minutes under running water.
- After swallowing: Seek immediate medical advice.
- · 4.2 Most important symptoms and effects, both acute and delayed

No further relevant information available.

· 4.3 Indication of any immediate medical attention and special treatment needed

No further relevant information available.

SECTION 5: Firefighting measures

- · 5.1 Extinguishing media
- Suitable extinguishing agents:

CO2, powder or water spray. Fight larger fire with alcohol resistant foam.

Use fire extinguishing methods suitable to surrounding conditions.

· 5.2 Special hazards arising from the substance or mixture

No further relevant information available.

- 5.3 Advice for firefighters
- · Protective equipment: No special measures required.

SECTION 6: Accidental release measures

- 6.1 Personal precautions, protective equipment and emergency procedures Not required.
- 6.2 Environmental precautions: No special measures required.
- 6.3 Methods and material for containment and cleaning up:

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust). Send for recovery or disposal in suitable receptacles.

6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

· 7.1 Precautions for safe handling

No special measures required.

Open and handle receptacle with care.

- · Information about fire and explosion protection: No special measures required.
- · 7.2 Conditions for safe storage, including any incompatibilities
- Storage:
- · Requirements to be met by storerooms and receptacles: Store only in the original receptacle.
- Information about storage in one common storage facility: Not required.
- Further information about storage conditions: Store in a cool place.
- · Storage class: 10

(Contd. on page 3)





Printing date 14.08.2017 Version number 11 Revision: 14.08.2017

Trade name: UHU Sekundenkleber CA 202 20 g

(Contd. of page 2)

· 7.3 Specific end use(s) No further relevant information available.

SECTION 8: Exposure controls/personal protection

- · Additional information about design of technical facilities: No further data; see item 7.
- · 8.1 Control parameters
- Ingredients with limit values that require monitoring at the workplace:

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

- Additional information: The lists valid during the making were used as basis.
- · 8.2 Exposure controls
- · Personal protective equipment:
- General protective and hygienic measures:

Do not eat, drink, smoke or sniff while working.

The usual precautionary measures are to be adhered to when handling chemicals.

· Protection of hands:

Protective gloves

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Preventive skin protection by use of skin-protecting agents is recommended.

After use of gloves apply skin-cleaning agents and skin cosmetics.

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

Material of gloves

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

Penetration time of glove material

The exact break trough time has to be found out by the manufacturer of the protective gloves and has to be observed.

· Eye protection: Not required.

SECTION 9: Physical and chemical properties

- · 9.1 Information on basic physical and chemical properties
- · General Information
- · Appearance:

Form: Fluid
Colour: Colourless
Odour: Characteristic
Odour threshold: Not determined.

pH-value: Not determined.

(Contd. on page 4)





Printing date 14.08.2017 Version number 11 Revision: 14.08.2017

Trade name: UHU Sekundenkleber CA 202 20 g

	(Contd. of page
 Change in condition Melting point/freezing point: Initial boiling point and boiling range 	Undetermined. : Undetermined.
Flash point:	125°C
Flammability (solid, gas):	Not applicable.
Ignition temperature:	
Decomposition temperature:	Not determined.
Auto-ignition temperature:	Product is not selfigniting.
Explosive properties:	Product does not present an explosion hazard.
Explosion limits: Lower: Upper:	Not determined. Not determined.
Vapour pressure:	Not determined.
Density at 20°C: Relative density Vapour density Evaporation rate	1.04087 g/cm³ Not determined. Not determined. Not determined.
Solubility in / Miscibility with water:	Not miscible or difficult to mix.
Partition coefficient: n-octanol/water:	Not determined.
Viscosity: Dynamic at 20°C: Kinematic:	20 mPas Not determined.
Solvent content: VOC (EC)	0.00 %
Solids content: 9.2 Other information	3.2 % All relevant physical data were determined for the mixture. All non determined data are not measurably not relevant for the characterization of the mixture.

SECTION 10: Stability and reactivity

- · 10.1 Reactivity No further relevant information available.
- · 10.2 Chemical stability
- Thermal decomposition / conditions to be avoided:

No decomposition if used according to specifications.

10.3 Possibility of hazardous reactions

Exothermic polymerisation.

Reacts with water.

Reacts with amines.

• 10.4 Conditions to avoid No further relevant information available.

(Contd. on page 5)



Page 5/6

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 14.08.2017 Version number 11 Revision: 14.08.2017

Trade name: UHU Sekundenkleber CA 202 20 g

(Contd. of page 4)

- 10.5 Incompatible materials: No further relevant information available.
- 10.6 Hazardous decomposition products: No dangerous decomposition products known.

SECTION 11: Toxicological information

- · 11.1 Information on toxicological effects
- · Acute toxicity Based on available data, the classification criteria are not met.
- · Primary irritant effect:
- Skin corrosion/irritation Based on available data, the classification criteria are not met.
- · Serious eye damage/irritation Based on available data, the classification criteria are not met.
- · Respiratory or skin sensitisation Based on available data, the classification criteria are not met.
- · Germ cell mutagenicity Based on available data, the classification criteria are not met.
- · Carcinogenicity Based on available data, the classification criteria are not met.
- Reproductive toxicity Based on available data, the classification criteria are not met.
- STOT-single exposure Based on available data, the classification criteria are not met.
- · STOT-repeated exposure Based on available data, the classification criteria are not met.
- · Aspiration hazard Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- · 12.1 Toxicity
- · Aquatic toxicity: No further relevant information available.
- 12.2 Persistence and degradability No further relevant information available.
- · 12.3 Bioaccumulative potential No further relevant information available.
- · 12.4 Mobility in soil No further relevant information available.
- Additional ecological information:
- · General notes:

Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water Do not allow product to reach ground water, water course or sewage system.

- 12.5 Results of PBT and vPvB assessment
- · PBT: Not applicable.
- vPvB: Not applicable.
- 12.6 Other adverse effects No further relevant information available.

SECTION 13: Disposal considerations

- · 13.1 Waste treatment methods
- Recommendation Disposal must be made according to official regulations.
- · European waste catalogue

08 04 09* waste adhesives and sealants containing organic solvents or other hazardous substances

- Uncleaned packaging:
- Recommendation: Disposal must be made according to official regulations.

EU-EN





Printing date 14.08.2017 Version number 11 Revision: 14.08.2017

Trade name: UHU Sekundenkleber CA 202 20 g

(Contd. of page 5)

SECTION 14: Transport information		
· 14.1 UN-Number · ADR, IMDG, IATA	Void	
· ADN	- Void	
· 14.2 UN proper shipping name · ADR, ADN, IMDG, IATA	Void	
· 14.3 Transport hazard class(es)		
· ADR, ADN, IMDG, IATA · Class	Void	
· 14.4 Packing group · ADR, IMDG, IATA	Void	
· 14.5 Environmental hazards: · Marine pollutant:	No	
· 14.6 Special precautions for user	Not applicable.	
· 14.7 Transport in bulk according to Ann of Marpol and the IBC Code	nex II Not applicable.	
· Transport/Additional information:	Not dangerous according to the abov specifications.	
· UN "Model Regulation":	Void	

SECTION 15: Regulatory information

- · 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
- · Directive 2012/18/EU
- · Named dangerous substances ANNEX I None of the ingredients is listed.
- · 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- · Department issuing SDS: UHU QESH
- Contact:

Frau A. Liar,

Herr Dr. C. Hanf

* Data compared to the previous version altered.

EU-EN