

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 12.02.2021

Version number 4

Revision: 12.02.2021

**SECTION 1: Identification of the substance/mixture and of the company/undertaking****1.1 Product identifier****Trade name:** UHU Alleskleber SUPER 7g Bl. DE**1.2 Relevant identified uses of the substance or mixture and uses advised against**

No further relevant information available.

**Application of the substance / the mixture** Adhesive**1.3 Details of the supplier of the safety data sheet****Manufacturer/Supplier:**

UHU GmbH &amp; Co.KG

Herrmannstraße 7

D-77815 Bühl (Baden)

Tel.: 0049-(0)7223-284-0

email: sds@boltonadhesives.com

Fax: 0049-(0)7223-284-245

**Further information obtainable from:** UHU QESH**1.4 Emergency telephone number:**

Tel.: + 49 (0) 30/19240 (Notruf)

Tel.: + 49 (0) 72 23/28 40

England and Wales (NHS Direct) 111

Schottland (NHS 24) 111

**SECTION 2: Hazards identification****2.1 Classification of the substance or mixture****Classification according to Regulation (EC) No 1272/2008**

The product is not classified, according to the CLP regulation.

**2.2 Label elements****Labelling according to Regulation (EC) No 1272/2008** Void**Hazard pictograms** Void**Signal word** Void**Hazard statements** Void**Additional information:**

Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

**2.3 Other hazards****Results of PBT and vPvB assessment****PBT:** Not applicable.**vPvB:** Not applicable.**SECTION 3: Composition/information on ingredients****3.2 Mixtures****Description:** Adhesive**Dangerous components:** Void**Additional information:** For the wording of the listed hazard phrases refer to section 16.

EU-EN

(Contd. on page 2)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 12.02.2021

Version number 4

Revision: 12.02.2021

**Trade name:** UHU Alleskleber SUPER 7g BI. DE

(Contd. of page 1)

**SECTION 4: First aid measures**

- **4.1 Description of first aid measures**
- **General information:** No special measures required.
- **After inhalation:**  
Supply fresh air; consult doctor in case of complaints.  
No special measures required.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:** Rinse opened eye for several minutes under running water.
- **After swallowing:** If symptoms persist consult doctor.
- **4.2 Most important symptoms and effects, both acute and delayed**  
No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

**SECTION 5: Firefighting measures**

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:** Use fire extinguishing methods suitable to surrounding conditions.
- **5.2 Special hazards arising from the substance or mixture**  
No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.

**SECTION 6: Accidental release measures**

- **6.1 Personal precautions, protective equipment and emergency procedures** Not required.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:** Pick up mechanically.
- **6.4 Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

**SECTION 7: Handling and storage**

- **7.1 Precautions for safe handling** Open and handle receptacle with care.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** None.
- **Storage class:** 11
- **7.3 Specific end use(s)** No further relevant information available.

EU-EN

(Contd. on page 3)

## Safety data sheet according to 1907/2006/EC, Article 31

Printing date 12.02.2021

Version number 4

Revision: 12.02.2021

**Trade name:** UHU Alleskleber SUPER 7g Bl. DE

(Contd. of page 2)

### SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**  
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**  
The usual precautionary measures are to be adhered to when handling chemicals.  
Wash hands before breaks and at the end of work.
- **Respiratory protection:** Not required.
- **Protection of hands:**  
The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.  
Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation
- **Material of gloves**  
Recommended thickness of the material: > 0,12 mm  
glove material: butyl rubber  
thickness of the glove material: 0,6 - 0,8 mm  
breakthrough time (maximum wearing time): 60 - 120 min.  
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.  
Nitrile rubber, NBR
- **Penetration time of glove material**  
For the mixture of chemicals mentioned below the penetration time has to be at least 10 minutes (Permeation according to EN 374 Part 3: Level 1).
- **Eye protection:** Not required.

### SECTION 9: Physical and chemical properties

- **9.1 Information on basic physical and chemical properties**
- **General Information**
- **Appearance:**

Form:	Pasty
Colour:	Colourless
Odour:	Characteristic
Odour threshold:	Not determined.
- **pH-value:** Not applicable.
- **Change in condition**

Melting point/freezing point:	Undetermined.
-------------------------------	---------------

(Contd. on page 4)

EU-EN

## Safety data sheet according to 1907/2006/EC, Article 31

Printing date 12.02.2021

Version number 4

Revision: 12.02.2021

**Trade name:** UHU Alleskleber SUPER 7g BI. DE

(Contd. of page 3)

<b>Initial boiling point and boiling range:</b> Undetermined.	
· <b>Flash point:</b>	>100 °C
· <b>Flammability (solid, gas):</b>	Not determined.
· <b>Decomposition temperature:</b>	Not determined.
· <b>Auto-ignition temperature:</b>	Product is not selfigniting.
· <b>Explosive properties:</b>	Product does not present an explosion hazard.
· <b>Explosion limits:</b>	
Lower:	Not determined.
Upper:	Not determined.
· <b>Vapour pressure:</b>	Not applicable.
· <b>Density at 20 °C:</b>	1.074 g/cm <sup>3</sup>
· <b>Relative density</b>	Not determined.
· <b>Vapour density</b>	Not applicable.
· <b>Evaporation rate</b>	Not applicable.
· <b>Solubility in / Miscibility with water:</b>	Insoluble.
· <b>Partition coefficient: n-octanol/water:</b>	Not determined.
· <b>Viscosity:</b>	
Dynamic at 20 °C:	400 mPas
Kinematic:	Not applicable.
· <b>9.2 Other information</b>	All relevant physical data were determined for the mixture. All non-determined data are not measurable or not relevant for the characterization of the mixture.

### SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**  
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

### SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.
- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.

(Contd. on page 5)

EU-EN

## Safety data sheet according to 1907/2006/EC, Article 31

Printing date 12.02.2021

Version number 4

Revision: 12.02.2021

**Trade name:** UHU Alleskleber SUPER 7g BI. DE

(Contd. of page 4)

- **Acute effects (acute toxicity, irritation and corrosivity)** Not applicable.
- **Sensitisation** Not applicable.
- **Repeated dose toxicity** Not applicable.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Not applicable.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

### SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**  
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water  
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

### SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**  
Must not be disposed together with household garbage. Do not allow product to reach sewage system.  
Disposal must be made according to official regulations.
- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

### SECTION 14: Transport information

- |                                       |               |
|---------------------------------------|---------------|
| · <b>14.1 UN-Number</b>               |               |
| · <b>ADR/ADN, IMDG, IATA</b>          | not regulated |
| · <b>ADN</b>                          | -             |
| · <b>ADN</b>                          | not regulated |
| · <b>14.2 UN proper shipping name</b> |               |
| · <b>ADR/ADN, ADN, IMDG, IATA</b>     | not regulated |

(Contd. on page 6)

EU-EN

## Safety data sheet according to 1907/2006/EC, Article 31

Printing date 12.02.2021

Version number 4

Revision: 12.02.2021

**Trade name:** UHU Alleskleber SUPER 7g BI. DE

(Contd. of page 5)

· <b>14.3 Transport hazard class(es)</b>	
· <b>ADR/ADN, ADN, IMDG, IATA</b>	
· <b>Class</b>	not regulated
· <b>14.4 Packing group</b>	
· <b>ADR/ADN, IMDG, IATA</b>	not regulated
· <b>14.5 Environmental hazards:</b>	Not applicable.
· <b>14.6 Special precautions for user</b>	Not applicable.
· <b>14.7 Transport in bulk according to Annex II of Marpol and the IBC Code</b>	Not applicable.
· <b>Transport/Additional information:</b>	Not dangerous according to the above specifications.
· <b>UN "Model Regulation":</b>	not regulated

### SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment – Annex II**
- None of the ingredients is listed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

### SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Department issuing SDS:** UHU QESH
- **Contact:** UHU QESH
- **Abbreviations and acronyms:**  
 ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)  
 IMDG: International Maritime Code for Dangerous Goods  
 IATA: International Air Transport Association  
 GHS: Globally Harmonised System of Classification and Labelling of Chemicals  
 EINECS: European Inventory of Existing Commercial Chemical Substances  
 ELINCS: European List of Notified Chemical Substances  
 CAS: Chemical Abstracts Service (division of the American Chemical Society)  
 PBT: Persistent, Bioaccumulative and Toxic  
 vPvB: very Persistent and very Bioaccumulative
- **\* Data compared to the previous version altered.**

EU-EN