

INSTRUCTION

Order No. : G50 / G100 / G150 / G 298



MOTOR WITH METAL GEARBOX

Conrad No. 498903 / 498905
498906 / 498907

For the most extreme load conditions

Miniature sizes with maximum power!

These gearboxes are suitable not only for 1:87 model building but for considerably larger scales as well. Different reduction gear ratios make it possible to achieve appropriate rotational speeds for all possible applications. You can reach all possible speeds, from 5 - 400 rpm. **The metallic gear wheels** provide maximum service life under the most extreme load conditions.



Gear ratio	Voltage in Volts				Art.No.
	0.5	2	4	6	
1:50 Type G50	30 rpm	150 rpm	300 rpm	400 rpm	G50
1:100 Type G100	15 rpm	75 rpm	150 rpm	225 rpm	G100
1:150 Type G150	10 rpm	50 rpm	100 rpm	150 rpm	G150
1:298 Type G298	5 rpm	25 rpm	50 rpm	75 rpm	G298