

Electronic housing - ME MAX 6,2 SP-TBUS 4-4 KMGY - 2869647

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Extra slim electronic housing for DIN rail bus connector, pitch 6.2 mm, 4 connection levels, 8-pos. with spring-cage connection

Product Features

- Easy device testing thanks to integrated test openings
- Housing can be labeled using standard laser systems
- IP20 shock protection
- Transparent front cover can be swiveled, reversed, and labeled
- Same PCB geometry for spring-cage and screw versions

Key commercial data

package_quantity	10
GTIN	4017918975142

Technical data

General

Housing type	Complete housing
Housing material	PBT
Color	light gray

Dimensions

Length	93.1 mm
Constructional height	101.2 mm
Width	6.2 mm
Pitch	6.2 mm

Technical data

Connection in acc. with standard	CUL
Nominal voltage U_N	300 V
Nominal current I_N	8 A
AWG/kcmil	24-12
Indicator1	CUL1
Inflammability class according to UL 94	V0
Number of positions	8

Connection data

Electronic housing - ME MAX 6,2 SP-TBUS 4-4 KMGY - 2869647

Technical data

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm

classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

approvals

UL Recognized / cUL Recognized / cULus Recognized /

Approval details

UL Recognized 

Electronic housing - ME MAX 6,2 SP-TBUS 4-4 KMGY - 2869647

approvals

cUL Recognized		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	8 A	8 A
mm ² /AWG/kcmil	24-12	24-12

cULus Recognized		
------------------	--	--

accessories

Screwdriver tools

SZF 1-0,6X3,5 - 1204517



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>