

Components of electronic housing - UM-PRO 72 COVER-R BK - 2200152

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Lateral element (right) with mounting foot for DIN rails for 72 mm wide UM-PRO profiles

The figure shows the 122 mm wide version

Product Features

- Plug-in assembly reduces assembly time and therefore saves costs
- Freely positionable covers offer flexibility
- Mounting close to the edge provides wiring advantages
- PE contacts that can be fitted on both sides ensure safety
- Additional foot elements increase mechanical stability
- Device communication can be extended by BUS cross contacting
- Well-designed profile geometry increases the form stability
- Labeling area for standard SK strips or TML marking foil (max. height 6 mm)
- Temperature range up to 100°C extends the possible fields of application (UM-PRO)
- Additional labeling of PCB with Phoenix Contact PMB module marker carrier (drill hole diameter 4 mm)

Key commercial data

package_quantity	10
GTIN	4046356547352

Technical data

General

Color	black
-------	-------

Technical data

Inflammability class according to UL 94	V0
---	----

classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506

Components of electronic housing - UM-PRO 72 COVER-R BK - 2200152

classifications

eCl@ss

eCl@ss 6.0	27182003
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC000721
ETIM 5.0	EC000721

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

approvals

UL Recognized /

Approval details



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>