

# Fuseholders 6.3 x 32mm (1¼" x ¼")



## Key Features

- 6.3 x 32mm fuses
- Screwdriver slot knob
- PC2 protection category
- 4.8, 6.3 and solder terminals
- Low profile bezel
- Snap in or threaded bushing mounting options

## Approvals and specifications

16A 250Vac (max fuse rating\*) T-55 to T+70 (ambient)  
Maximum dissipation wattage: 4W



6.3A UL 94V2 UL file E92075 CSA file LR44770

These products comply with safety category PC2.


\*Users should be aware of the de-rating factors published by specialist manufacturers of fuses.

Fuseholders with in-line termination have combination (4,8/6,3) terminals. It has not been possible to show both views here. Units with right angle terminals have user specified end terminals and combination mid-body terminals.




## Terminal

**C**




6.3 x 0.8

**D**




6.3 x 0.8  
Right angle

**T**



4.8 x 0.8  
Solder

**U**



4.8 x 0.8  
Solder

## Body

**0345**

(C terminal shown)  
Screwdriver release



**0345**

(D terminal shown)  
Screwdriver release



**0347**

(T terminal shown)  
Screwdriver release




**0347**

(U terminal shown)  
Screwdriver release




## Options

**RA**



Panel thickness  
0.8 - 2.0mm for snap fit  
0.8 - 7.0mm for screw to  
panel fixing


**RD**




Panel thickness  
0.8 - 2.0mm for snap fit  
0.8 - 7.0mm for screw to  
panel fixing

## Dimensions


0345 (C terminal shown)




0345 (D terminal shown)



0347 (C terminal shown)



0347 (D terminal shown)



Optional metal fixing nut available for 0347