

# Electronic housing - ME MAX 17,5 SF G 2-2 KMGY - 2901369

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Component housing, Complete housing, Cross connection: DIN rail bus connector, Color: light gray, Width: 17.5 mm, Constructional height: 70.4 mm, Number of positions cross connector: 5

## Product Features

- Labels for additional labeling as an option
- DIN rail bus connector as an option
- Plug-in connection with screw, spring-cage or fast connection technology
- Large PCB surface despite compact housing dimensions
- Large front surface for high-pos. plugs or operating and setting elements
- The fitted cover is easy to adapt and print
- Easy module replacement without interrupting the contact chain
- Transparent front cover can be swiveled
- Functional earth ground contact as an option
- Fixed or plug-in connection technology can be combined on up to three connection levels, with different pitches

## Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4046356178525

## Technical data

### General

<b>Housing type</b>	Component housing
<b>Housing material</b>	Polyamide
<b>Color</b>	light gray

### Ambient conditions

<b>Ambient temperature (operation)</b>	-40 °C (depending on power dissipation)
--	---

### Dimensions

<b>Length</b>	85 mm
<b>Constructional height</b>	70.4 mm
<b>Width</b>	17.5 mm

### Technical data

<b>Inflammability class according to UL 94</b>	V0
<b>Power dissipation at 20°C in the horizontal mounting position</b>	3.2 W 5.9 W

# Electronic housing - ME MAX 17,5 SF G 2-2 KMGY - 2901369

## classifications

### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501


## approvals

---

UL Recognized / cUL Recognized / cULus Recognized /

---


### Approval details



## Drawings

# Electronic housing - ME MAX 17,5 SF G 2-2 KMGY - 2901369

Dimensioned drawing



A = 70.4 mm; B = 17.5 mm; C = 85 mm

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>