


**Features**

- 1 Pole - Low profile (15.4 mm height)
- 43.41 - 1 Pole, 10 A (3.2 mm pin pitch)
- 43.41-0300 - 1 Pole NO, 10 A (5 mm pin pitch)
- 43.61-0300 - 1 Pole NO, 16 A (5 mm pin pitch)

PCB mount - direct or via PCB socket (43.41 version)

- Sensitive DC coil:
  - 250 mW (10 A version)
  - 400 mW (16 A version)
- Very high coil-contact isolation 10 mm, 6 kV (1.2/50 µs)
- Cadmium Free contacts (preferred version)
- Flux proof: RT II standard, (RT III option)



FOR UL RATINGS SEE:  
"General technical information" page V

**43.41**



- 3.2 mm contact pin pitch
- 1 Pole CO, 10 A
- PCB direct or via socket

**43.41-0300**




- 5 mm contact pin pitch
- 1 Pole NO, 10 A
- PCB mount


**43.61-0300**




- 5 mm contact pin pitch
- 1 Pole NO, 16 A
- PCB mount



Copper side view



Copper side view



Copper side view

<b>Contact specification</b>				
Contact configuration		1 CO (SPDT)	1 NO (SPST-NO)	1 NO (SPST-NO)
Rated current/Maximum peak current	A	10/15	10/15	16/25
Rated voltage/Maximum switching voltage	V AC	250/400	250/400	250/400
Rated load AC1	VA	2,500	2,500	4,000
Rated load AC15 (230 V AC)	VA	500	500	750
Single phase motor rating (230 V AC)	kW	—	—	—
Breaking capacity DC1: 30/110/220 V	A	10/0.3/0.12	10/0.3/0.12	16/0.3/0.12
Minimum switching load	mW (V/mA)	300 (5/5)	300 (5/5)	300 (5/5)
Standard contact material		AgNi	AgNi	AgNi
<b>Coil specification</b>				
Nominal voltage (U <sub>N</sub> )	V AC (50/60 Hz)	—	—	—
	V DC	3 - 6 - 9 - 12 - 18 - 24 - 36 - 48	3 - 6 - 9 - 12 - 18 - 24 - 36 - 48	12 - 24 - 48
Rated power AC/DC	VA (50 Hz)/W	—/0.25	—/0.25	—/0.4
Operating range	AC	—	—	—
	DC	(0.7...1.5)U <sub>N</sub>	(0.7...1.5)U <sub>N</sub>	(0.7...1.2)U <sub>N</sub>
Holding voltage	AC/DC	—/0.4 U <sub>N</sub>	—/0.4 U <sub>N</sub>	—/0.4 U <sub>N</sub>
Must drop-out voltage	AC/DC	—/0.05 U <sub>N</sub>	—/0.05 U <sub>N</sub>	—/0.05 U <sub>N</sub>
<b>Technical data</b>				
Mechanical life AC/DC	cycles	—/10 · 10 <sup>6</sup>	—/10 · 10 <sup>6</sup>	—/10 · 10 <sup>6</sup>
Electrical life at rated load AC1	cycles	100 · 10 <sup>3</sup>	100 · 10 <sup>3</sup>	50 · 10 <sup>3</sup>
Operate/release time	ms	6/4	6/2	6/2
Insulation between coil and contacts (1.2/50 µs)	kV	6 (10 mm)	6 (10 mm)	6 (10 mm)
Dielectric strength between open contacts	V AC	1,000	1,000	1,000
Ambient temperature range	°C	—40...+85	—40...+85	—40...+85
Environmental protection		RT II	RT II	RT II

**Approvals** (according to type)



### Ordering information

Example: 43 series low-profile PCB relay, 1 CO (SPDT), 24 V DC coil.

A



- Series** \_\_\_\_\_
- Type** \_\_\_\_\_  
 4 = PCB - 3.2 mm pinning (CO/SPDT, 10 A)  
 PCB - 5 mm pinning (NO/SPST-NO, 10 A)  
 6 = PCB - 5 mm pinning (NO/SPST-NO, 16 A)
- No. of poles** \_\_\_\_\_  
 1 = 1 pole
- Coil version** \_\_\_\_\_  
 7 = Sensitive DC (only for 43.41)  
 9 = DC (only for 43.61)
- Coil voltage** \_\_\_\_\_  
 See coil specifications

- A: Contact material**  
 0 = AgNi  
 2 = AgCdO  
 4 = AgSnO<sub>2</sub>  
 5 = AgNi + Au
- B: Contact circuit**  
 0 = CO (SPDT) - (for 43.41 only)  
 3 = NO (SPST)
- C: Options**  
 0 = None
- D: Special versions**  
 0 = Flux proof (RT II)  
 1 = Wash tight (RT III)

**Selecting features and options: only combinations in the same row are possible.**  
 Preferred selections for best availability are shown in **bold**.


Type	Coil version	A	B	C	D
43.41	sensitive DC	<b>0</b> - 2 - 4 - 5	<b>0</b> - 3	<b>0</b>	<b>0</b> - 1
43.61	DC	<b>0</b> - 2 - 4	<b>3</b>	<b>0</b>	<b>0</b>

### Technical data


Insulation according to EN 61810-1					
Nominal voltage of supply system	V AC	230/400			
Rated insulation voltage	V AC	250	400		
Pollution degree		3	2		
Insulation between coil and contact set					
Type of insulation		Reinforced (10 mm)			
Overvoltage category		III			
Rated impulse voltage	kV (1.2/50 µs)	6			
Dielectric strength	V AC	4,000			
Insulation between open contacts					
Type of disconnection		Micro-disconnection			
Dielectric strength	V AC/kV (1.2/50 µs)	1,000/1.5			
Conducted disturbance immunity					
Burst (5...50)ns, 5 kHz, on A1 - A2		EN 61000-4-4	level 4 (4 kV)		
Surge (1.2/50 µs) on A1 - A2 (differential mode)		EN 61000-4-5	level 3 (2 kV)		
Other data					
Bounce time: NO/NC	ms	3/6			
Vibration resistance (5...55)Hz: NO/NC	g	15/3			
Shock resistance	g	15			
Power lost to the environment	without contact current	W	0.25 (43.41)	0.4 (43.61)	
	with rated current	W	1.3 (43.41)	2 (43.61)	
Recommended distance between relays mounted on PCB	mm	≥ 5			

**Contact specification**

**F 43 - Electrical life (AC) v contact current**



**H 43 - Maximum DC1 breaking capacity**




- When switching a resistive load (DC1) having voltage and current values under the curve, an electrical life of  $\geq 100 \cdot 10^3$  for 43.41 and  $\geq 50 \cdot 10^3$  for 43.61 can be expected.
- In the case of DC13 loads, the connection of a diode in parallel with the load will permit a similar electrical life as for a DC1 load.  
Note: the release time for the load will be increased.

**Coil specifications**

**DC coil data - 0.25 W sensitive (type 43.41)**

Nominal voltage $U_N$	Coil code	Operating range		Resistance $R$	Rated coil consumption $I$ at $U_N$
		$U_{min}$	$U_{max}$		
V		V	V	$\Omega$	mA
3	7.003	2.2	4.5	36	83.5
6	7.006	4.2	9	150	40
9	7.009	6.5	13.5	324	27.7
12	7.012	8.4	18	580	20.7
18	7.018	13	27	1,300	13.8
24	7.024	16.8	36	2,200	10.9
36	7.036	25.2	54	5,200	6.9
48	7.048	33.6	72	9,200	5.2

**R 43 - DC coil operating range v ambient temperature**



- 1 - Max. permitted coil voltage.
- 2 - Min. pick-up voltage with coil at ambient temperature.

**DC coil data - 0.4 W standard (type 43.61)**

Nominal voltage $U_N$	Coil code	Operating range		Resistance $R$	Rated coil consumption $I$ at $U_N$
		$U_{min}$	$U_{max}$		
V		V	V	$\Omega$	mA
12	9.012	8.4	14.4	360	33.3
24	9.024	16.8	28.8	1,400	17.1
48	9.048	33.6	57.6	5,760	8.3

A




95.23

Approvals  
(according to type):



<b>PCB socket</b> (for changeover contacts only)	<b>95.23 (blue)</b>	<b>95.23.0 (black)</b>
For relay type	43.41	43.41
<b>Accessories</b>		
Metal retaining clip (supplied with socket - packaging code SNA)	095.43	
<b>Technical data</b>		
Rated values	10 A - 250 V	
Insulation	6 kV (1.2/50 µs) between coil and contacts	
Protection category	IP 20	
Ambient temperature	°C -40...+70	



Copper side view

### Packaging codes

How to code and identify retaining clip and packaging options for sockets.

Example:

