



QQGQ2.E214596
Power Supplies, Information Technology Equipment Including Electrical
Business Equipment - Component

Page Bottom

Power Supplies, Information Technology Equipment Including Electrical Business
Equipment - Component

See General Information for Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

PHOENIX CONTACT GMBH & CO KG
 FLACHSMARKTSTRASSE 8
 32825 BLOMBERG, GERMANY

E214596

Model No.	Rated Input			Max Output				SP	EP	FC	GC
	Volts	Hz	SC	V	A	VA	OC				
OPS1020.0, MINI-PS-100-240AC/24DC/2											
	100-240ac 90-350dc	50-60	0	28.1	5.2	91	3	60950	15B	5	2
MINI-PS-100-240AC/10-15DC/2											
	100-240ac 90-350dc	50-60	0	15dc	2	30	3	60950-1	15B	5	2
MINI-PS-100-240AC/12DC/2/SO1, 2866912											
	100-240ac 90-350dc	50-60	0	12dc	2	24	3	60950-1	15B	5	2
MINI-PS-100-240AC/2x15DC/1[*r]											
	100-240 ac or 90-350 dc	50-60	0,4	-15dc	1	-	3	60950	-	0	-
				15dc	1	-	3				
MINI-PS-100-240AC/5DC/3											
	100-240ac 90-350dc	50-60	0	5.6	6.2	28.5	3	60950	15b	5	2
OPS1025.2											
	100-240ac	50-60	-	24dc	2.5	-	-	-	-	-	-
OPS1042.2											
	100-240ac	50-60	-	24dc	4.2	-	-	-	-	-	-
QSPS-DH-1-75, STEP-PS/277AC/24DC/2.5/LU, STEP-PS/277AC/24DC/2.5/xx whereby xx may be any alphanumeric character.											
	100-277 Vac; 100-250 Vdc	50/60	0	24.25dc	3.3	80	1	60950-1, 2nd Ed+AM1+AM2	20B	-	2
STEP-DIODE/5-24DC/2x5/1x10											
	5-24dc	-	-	5-24dc	0-10	-	-	60950-1	-	-	-
STEP-PS/1AC/12DC/1[*r]											
	100-240 ac 95-250 dc	50-60	0	12dc	1	-	1	60950-1 2nd	20B	5	2
STEP-PS/1AC/12DC/1.5											
	100-240 ac 95-250 dc	50-60	0	12.1dc	2.2	22.3	0	60950-1	20B	5	2
STEP-PS/1AC/12DC/1.5/FL											
	100-240 ac 95-250 dc	50-60	0	12.1dc	2.2	22.3	0	60950-1	20B	5	2
STEP-PS/1AC/12DC/3.0[*r]											
		50-60	0	12dc	3	36	3	60950-1	20B	5	2

	100-240 Vac / 95-250 Vdc											
STEP-PS/1AC/12DC/5.0[*r]												
	100-240 Vac; 95-250 Vdc	50-60	0	12dc	5	60	3	60950-1	20B	5	2	
STEP-PS/1AC/15DC/4.0[*r]												
	100-240 Vac; 95-250 Vdc	50-60	0	15dc	4	60	3	60950-1	20B	5	2	
STEP-PS/1AC/24DC/0.5[*r]												
	100-240 ac 95-250 dc	50-60	0	24dc	0.5	-	1	60950-1 2nd	20B	5	2	
STEP-PS/1AC/24DC/0.75												
	100-240 ac 95-250 dc	50-60	0	24dc	0.75	18	3	60950-1	20B	5	2	
STEP-PS/1AC/24DC/0.75/FL[*r]												
	100-240 ac 95-250 dc	50-60	0	24dc	0.75	-	3	60950-1	-	0	2	
STEP-PS/1AC/24DC/1.75 (/XX), XX is optional and can be any character or number[*r]												
	100-240 Vac / 95-250 Vdc	50-60	0	24dc	1.75	42	3	60950-1	20B	5	2	
STEP-PS/1AC/24DC/2.5												
	100-240 ac 95-250 dc	50-60	0	24dc	2.5	60	3	60950-1	20B	5	2	
STEP-PS/1AC/24DC/3.8/C2LPS												
	100-240 Vac, 95-250 Vdc	50-60	0	24dc	5.0	92.3	1	60950-1	20B	5	2	
STEP-PS/1AC/24DC/4.2[*r]												
	100-240 Vac; 95-250Vdc	50-60	0	24dc	4.2	100.8	3	60950-1	20B	5	2	
STEP-PS/1AC/48DC/2												
	100-240 Vac; 95-250 Vdc	50-60	0	48dc	2.0	96	3	60950-1	20B	5	2	
STEP-PS/1AC/5DC/2[*r]												
	100-240 Vac; 95-250 Vdc	50-60	0	5dc	2.0	10	3	60950-1	20B	5	2	
STEP-PS/1AC/5DC/6.5[*r]												
	100-240 Vac; 95-250 Vdc	50-60	0	5dc	6.5	32.5	3	60950-1	20B	5	2	
STEP-PS/277AC/24DC/3.5[*r]												
	100-240 Vac, 95-250 Vdc	50-60	0	24dc	3.5	84	1	60950-1, 2nd Ed + AM1	20B	5	2	
STEP-PS/48AC/24DC/0.5[*r]												
	48ac	50-60	0	24dc	0.5	-	1	60950-1 2nd	20B	5	2	
STEP-UPS/12DC/12DC/4[*r]												
	12dc	-	3	12dc	4 @ amb. 40°C	-	3	60950-1 2nd	-	5	-	
				12dc	5 @ amb. 35°C	-	3					
STEP-UPS/24DC/24DC/3[*r]												
	24dc	-	3	24dc	3 @ amb. 40°C	-	3	60950-1 2nd	-	5	-	
				24dc	4 @ amb. 35°C	-	3					
UNO-DIODE/5-24DC/2x10/1x20[*r]												
	5-24dc	-	3	5-24dc	max. 20	max. 480	3	60950-1, 2nd Ed + AM1	-	5	-	
UNO-PS/1AC/12DC/100W[*r]												

	100-240 Vac	50-60	0	12dc	8.33	100	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/1AC/12DC/30W[*r]											
	100-240 Vac	50-60	0	12dc	2.5	30	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/1AC/12DC/55W[*r]											
	100-240 Vac	50-60	0	12dc	4.6	55	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/1AC/15DC/100W[*r]											
	100-240 Vac	50-60	0	15dc	6.66	100	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/1AC/15DC/30W[*r]											
	100-240 Vac	50-60	0	15dc	2.0	30	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/1AC/15DC/55W[*r]											
	100-240 Vac	50-60	0	15dc	3.7	55	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/1AC/24DC/100W[*r]											
	100-240 Vac	50-60	0	24dc	4.2	100	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/1AC/24DC/150W[*r]											
	100-240Vac	50-60	-	24dc	6.25	150	3	60950-1, 2nd Ed + AM1	20B	-	-
UNO-PS/1AC/24DC/240W											
	100-240 Vac	50-60	0	29.6dc	10.9	260	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/1AC/24DC/30W[*r]											
	100-240 Vac	50-60	0	24dc	1.25	30	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/1AC/24DC/55W[*r]											
	100-240 Vac	50-60	0	24dc	2.3	55	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/1AC/24DC/60W[*r]											
	100-240 Vac	50-60	0	24dc	2.5	60	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/1AC/24DC/90W/C2LPS[*r]											
	100-240 Vac	50-60	0	24dc	3.75	90	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/1AC/48DC/100W[*r]											
	100-240 Vac	50-60	0	48dc	2.1	100	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/1AC/48DC/60W[*r]											
	100-240 Vac	50-60	0	48dc	1.25	60	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/1AC/5DC/25W[*r]											
	100-240 Vac	50-60	0	5dc	5	25	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/1AC/5DC/40W[*r]											
	100-240 Vac	50-60	0	5dc	8	40	3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-PS/2AC/24DC/90W/C2LPS											
	400-500 Vac	50-60	0	25.2dc	5.07	92.24	1,3	60950-1, 2nd Ed + AM1	20B	5	2
UNO-UPS/24DC/24DC/60W[*r]											
	24dc	-	3	24dc	2.5	-	3	60950-1, 2nd Ed+AM1+AM2	-	8	-

[*r] - Output values are rated.

Marking: Company name and model designation on the product or on the smallest unit container in which the product is packaged.

Last Updated on 2015-08-05

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2016 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2016 UL LLC".