

Philips screwdriver - SF-PH 2-100 - 1212560

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Screwdriver, PH crosshead (lasered), uninsulated, size: PH 2 x 100, 2-component grip, with non-slip grip

Product Features

- VDE approval
- Screwdrivers for Phillips screws with Pozidriv and Phillips Recess screw head

Key commercial data

package_quantity	10
GTIN	4046356589956

Technical data

Dimensions

Length (b)	205 mm
Width (a)	37 mm
Blade height	100 mm

General

Design	Phillips
Type	Straight
Material	Alloyed tool steel
Test standard	DIN ISO 8764-1

classifications

eCl@ss

eCl@ss 4.0	21040401
eCl@ss 4.1	21040401
eCl@ss 5.0	21040401
eCl@ss 5.1	21040401
eCl@ss 6.0	21040401
eCl@ss 7.0	21040409
eCl@ss 8.0	21040409

ETIM

ETIM 4.0	EC000144
-----------------	----------

Philips screwdriver - SF-PH 2-100 - 1212560

classifications

ETIM

ETIM 5.0	EC000144
-----------------	----------

UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

approvals

GOST /

Approval details



Drawings

Philips screwdriver - SF-PH 2-100 - 1212560

Pictogram

