

Productname : DIESEL ADDITIVE  
 Ref.Nr.: BDS002245\_3\_20171012 (EN)

Creationdate : 12.10.17 Version : 1.0  
 Replaces:

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**DIESEL ADDITIVE**  
 Bulk

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Additives

### 1.3. Details of the supplier of the safety data sheet

**CRC Industries Europe bvba**  
 Touwslagerstraat 1  
 9240 Zele  
 Belgium  
 Tel.: +32(0)52/45.60.11  
 Fax.: +32(0)52/45.00.34  
 E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Laurinkatu 57 A 23 B, 08100 Lohja	+358/(19)32.921	
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Laxfiskevägen 16, 433 38 Partille	0046/31 706 84 80	0046/31 27 39 91

### 1.4. Emergency telephone number

**CRC Industries Europe, Belgium:** Tel.: +32(0)52/45.60.11 (office hours)

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to Regulation (EC) No 1272/2008

**Physical:** Not classified  
 Classification is based on test data.  
**Health:** Aspiration Hazard Category 1  
 May be fatal if swallowed and enters airways.



**Productname :** DIESEL ADDITIVE **Creationdate :** 12.10.17 Version : 1.0  
**Ref.Nr.:** BDS002245\_3\_20171012 (EN) **Replaces:**

Classification based on calculation method.

**Environment:** Not classified


Classification based on calculation method.

**Other hazards :** Repeated exposure may cause skin dryness or cracking.

## 2.2. Label elements

### Labelling according to Regulation (EC) No 1272/2008

**Product identifier:** Contains:  
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics

**Hazard pictogram(s):** 

**Signal word:** Danger

**Hazard statement(s):** H304 : May be fatal if swallowed and enters airways.

**Precautionary statement(s):** P102 : Keep out of reach of children.  
P301/310 : IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.  
P331 : Do NOT induce vomiting.  
P405 : Store locked up.  
P501-2 : Dispose of contents/container to an authorised waste collection point.

**Supplemental Hazard information:** Repeated exposure may cause skin dryness or cracking.

## 2.3. Other hazards

No information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

### 3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics	01-2119456620-43	-	(926-141-6)	75-100	Asp. Tox. 1	H304	B,Q
2-ethylhexan-1-ol	01-2119487289-20	104-76-7	203-234-3	1-5	Acute Tox. 4, Skin Irrit. 2, Eye Irrit. 2, STOT SE 3	H315,H319,H332,H335	B
Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, < 2% aromatics	01-2119457273-39	-	(918-481-9)	1-5	Asp. Tox. 1	H304	Q
<b>Explanation notes</b>							
B : substance with national established workplace exposure limit							
Q : The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.							

(\* Explanation phrases : see chapter 16)

Productname : DIESEL ADDITIVE  
Ref.Nr.: BDS002245\_3\_20171012 (EN)

Creationdate : 12.10.17 Version : 1.0  
Replaces:

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

<b>Contact with eyes :</b>	If substance has got into eyes, immediately wash out with plenty of water for several minutes Seek medical attention if irritation persists
<b>Contact with skin :</b>	Wash with water and soap. Seek medical attention if irritation persists
<b>Inhalation :</b>	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
<b>Ingestion :</b>	IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician. Do NOT induce vomiting.

### 4.2. Most important symptoms and effects, both acute and delayed

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	Mildly irritating to skin Symptoms : redness and pain
<b>Eye contact :</b>	Mildly irritating to eyes Symptoms : redness and pain

### 4.3. Indication of any immediate medical attention and special treatment needed

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

foam, carbon dioxide or dry agent

### 5.2. Special hazards arising from the substance or mixture

May form explosive vapour/air mixtures  
Forms hazardous decomposition products  
CO,CO2

### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes



Productname : DIESEL ADDITIVE  
Ref.Nr.: BDS002245\_3\_20171012 (EN)

Creationdate : 12.10.17 Version : 1.0  
Replaces:

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing including eye/face protection.  
Ground/bond container and receiving equipment.  
Use explosion-proof electrical/ventilating/lighting/.../equipment.

### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses

### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

### 6.4. Reference to other sections

For further information see section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.

### 7.2. Conditions for safe storage, including any incompatibilities

Keep container tightly closed, in a cool, well ventilated place.  
Keep out of reach of children.

### 7.3. Specific end use(s)

Additives

## SECTION 8: Exposure controls/personal protection



**Productname :** DIESEL ADDITIVE  
**Ref.Nr.:** BDS002245\_3\_20171012 (EN)

**Creationdate :** 12.10.17 Version : 1.0  
**Replaces:**

## 8.1. Control parameters

### Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
2-ethylhexan-1-ol	104-76-7	TWA	1 ppm

## 8.2. Exposure controls

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. It is good practice to wear gloves and to provide adequate ventilation whenever using the product. In all cases handle and use the product in accordance with good industrial hygiene practices.
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with organic gas/vapor cartridge (type A)
<b>hands and skin :</b>	Wear suitable protective gloves against chemicals. Check the appropriateness of the recommended gloves for your own particular conditions of use and replace gloves regularly after check for signs of damage or defects.
Recommended gloves:	Nitrile
<b>eyes :</b>	Wear safety eyewear according to EN 166.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

<b>Apperance : physical state :</b>	Liquid.
<b>colour :</b>	Brown.
<b>odour :</b>	Characteristic odor.
<b>pH :</b>	Not applicable.
<b>Boiling point/range :</b>	Not available.
<b>Flash point :</b>	65 °C
<b>Evaporation rate :</b>	Not available.
<b>Explosion limits : upper limit :</b>	Not available.
<b>lower limit :</b>	Not available.
<b>Vapour pressure :</b>	Not available.
<b>Relative density :</b>	0.809 g/cm <sup>3</sup> (@ 20°C).
<b>Solubility in water :</b>	Insoluble in water
<b>Auto-ignition :</b>	> 200 °C
<b>Viscosity :</b>	Not available.

### 9.2. Other information



Productname : DIESEL ADDITIVE  
Ref.Nr.: BDS002245\_3\_20171012 (EN)

Creationdate : 12.10.17 Version : 1.0  
Replaces:

VOC = volatile organic  
compounds 785 g/l

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials

Strong oxidising agent

### 10.6. Hazardous decomposition products

CO,CO2

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

acute toxicity:	based on available data the classification criteria are not met
skin corrosion/irritation:	based on available data the classification criteria are not met
serious eye damage/irritation:	based on available data the classification criteria are not met
respiratory or skin sensitisation:	based on available data the classification criteria are not met
germ cell mutagenicity:	based on available data the classification criteria are not met
carcinogenicity:	based on available data the classification criteria are not met
toxicity for reproduction:	based on available data the classification criteria are not met
STOT-single exposure:	based on available data the classification criteria are not met
STOT repeated exposure:	based on available data the classification criteria are not met
aspiration hazard:	May be fatal if swallowed and enters airways.

### Information on likely routes of exposure:

Inhalation : Inhalation of solvent vapours may give rise to nausea, headaches and



**Productname :** DIESEL ADDITIVE  
**Ref.Nr.:** BDS002245\_3\_20171012 (EN)

**Creationdate :** 12.10.17 Version : 1.0  
**Replaces:**

<b>Ingestion :</b>	dizziness After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
<b>Skin contact :</b>	Prolonged skin contact will result in defatting of the skin, leading to irritation, and in some cases, dermatitis
<b>Eye contact :</b>	May cause irritation.

**Toxicological data :**

Hazardous ingredient	CAS-nr.	method	
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics	-	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	>5000 mg/kg
		LD50 derm.rabit	> 5000 mg/kg

**SECTION 12: Ecological information****12.1. Toxicity**

Not classified

**Ecotoxicological data:**

Hazardous ingredient	CAS-nr.	method	
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics	-	IC50 algae	1000 mg/l
		LC50 fish	1000 mg/l
		EC50 daphnia	1000 mg/l

**12.2. Persistence and degradability**

No information available

**12.3. Bioaccumulative potential**

No information available

**12.4. Mobility in soil**

Insoluble in water

**12.5. Results of PBT and vPvB assessment**

No information available

**12.6. Other adverse effects**

No information available



Productname : DIESEL ADDITIVE  
Ref.Nr.: BDS002245\_3\_20171012 (EN)

Creationdate : 12.10.17 Version : 1.0  
Replaces:

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

**Product :** This material and its container must be disposed of in a safe way.  
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

**Contaminated packaging :** Disposal should be in accordance with local, state or national legislation

## SECTION 14: Transport information

### 14.1. UN number

UN-number : Not classified as hazardous for transport

### 14.2. UN proper shipping name

Proper shipping name: Not applicable.

### 14.3. Transport hazard class(es)

Class: Not applicable.  
ADR/RID - Classification code: Not applicable.

### 14.4. Packing group

Packing group: Not applicable.

### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally hazardous: No

### 14.6. Special precautions for user

IMDG - Ems: Not applicable.

### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture





**Productname :** DIESEL ADDITIVE  
**Ref.Nr.:** BDS002245\_3\_20171012 (EN)

**Creationdate :** 12.10.17 Version : 1.0  
**Replaces:**

The Safety Data Sheet is compiled according to the current European requirements.  
Regulation (EC) No 1907/2006 (REACH)  
Regulation (EC) No 1272/2008 (CLP)

## 15.2. Chemical safety assessment

No information available

## SECTION 16: Other information

\*Explanation hazard statements: H304 : May be fatal if swallowed and enters airways.  
H315 : Causes skin irritation.  
H319 : Causes serious eye irritation.  
H332 : Harmful if inhaled.  
H335 : May cause respiratory irritation.

acronyms and synonyms: TWA = time weight average  
STEL = short time exposure limit  
VOC = volatile organic compounds  
PBT = persistent bioaccumulative toxic  
vPvB = very persistent very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.