




PANEL CUT-OUT



SPECIFICATION

A: MATERIAL:


- 1. HOUSING: PC, UL 94V-0
- 2. TERMINAL: COPPER ALLOY, TIN PLATED

B: CHARACTERISTICS:

- 1. RATING: 10A 250V~ EUROPE
10A 250V~ NORTH AMERICA*
- 2. INSULATION RESISTANCE : 100MΩ MIN. AT 500V DC
- 3. ELECTRIC STRENGTH: AC 2000V FOR ONE MINUTE
- 4. FUSE: φ5X20mm

C: APPROVALS: UL, CUL, VDE, & CCC

D: EQUIVALENT CIRCUIT



E: ORDERING INFORMATION:

P/N	SWITCH TYPE	SOCKET'S TERMINAL	SWITCH'S TERMINAL
0717-1S-PQ10N-A	Non-illuminated		
PANEL THICKNESS 1,0 MM			

CONRAD electronic SE

CE-Art.Nr. 501637

Wippschalter, unbeleuchtet mit [O -] -Bedruckung

Rocker-Switch, unilluminated, marking [O -]

TOLERANCE UNLESS OTHERWISE MARKED
 DIMENSION: .000 : ±0.1
 .00 : ±0.2
 .0 : ±0.3
 ANGULAR: ±3°

A 4 UNIT mm SCALE 1:1 SHEET 1 of 1

PART NO.: 0717-1S	NAME: AC INLET 3P WITH SWITCH & FUSE HOLDER (SNAP-IN)
MATERIAL: SEE ABOVE	SPEC.: IEC 60320-1, C14 IEC 60127-6
APPROVED:	DESIGNER:
NOTE: SHEET 5 of 6 DATE: 2008-08-06 DRAWN BY:	

