

8 A MINIATURE POWER RELAY IN DS RELAY SERIES

DSP RELAY

FEATURES

- · Power types added to DS relay series
- High switching capacity:
- 1a: 8 A 250 V AC / 1a1b, 2a: 5 A 250 V AC
- High sensitivity: 190 mW pick-up power
- High contact welding resistance
- Latching types available
- High breakdown voltage 3,000 Vrms between contacts and coil 1,000 Vrms between open contacts **Meeting FCC Part 68**
- · Sealed types are standard

mm inch

SPECIFICATIONS (at 20°C 68°F)

Contact				
Arrangemen	t	1a	1a1b	2a
Contact mat	erial	AgSnO ₂ type		
	t resistance, max. drop 6 V DC 1A)	30 mΩ		
Nominal swi	tching capacity	8A 250 VAC 5A 30 VDC	5A 250 VAC	
	Max. switching power	2,000 VA 150 W	1,250 VA 150 W	
Rating (resistive)	Max. switching voltage	250 V AC, 30 V DC		
(Tesistive)	Max. switching current	8 A	5 A	
	Min. switching capacity#1	10 mA, 5 V DC		C
Expected life (min.	Mechanical (at 180 cpm)	5×10 ⁷		
operations)	Electrical	105		

Coil (polarized) (at 20°C 68°F)

	Single side stable	192 mW
Minimum operating power	1 coil latching	96 mW
	2 coil latching	192 mW
	Single side stable	300 mW
Nominal operating power	1 coil latching	150 mW
power	2 coil latching	300 mW

Note: All specifications are based on the condition of 25°C 77°F. 50% R.H. unless otherwise specified.

#1 This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.

Remarks

- Specifications will vary with foreign standards certification ratings.
- *1 Measurement at same location as "Initial breakdown voltage" section
- *2 Detection current: 10mA
- *3 Excluding contact bounce time
- \star4 Half-wave pulse of sine wave: 11ms; detection time: 10 μs *5 Half-wave pulse of sine wave: 6ms
- *6 Detection time: 10us
- *7 Refer to 6. Conditions for operation, transport and storage mentioned in AMBIENT ENVIRONMENT (p. 19, Relay Technical Information).

Characteristics

Characteri	STICS		
Max. operat	ing speed	30 cps. at rated load	
Initial insula	tion resistance*1	Min. 1,000 MΩ at 500 V DC	
	Between open contacts	1,000 Vrms	
Initial breakdown	Between contact sets	2,000 Vrms (1a1b, 2a)	
voltage*2	Between contacts and coil	3,000 Vrms	
Surge voltaç coil	ge between contacts and	Min. 5,000 V	
Set time*3 (a	at nominal voltage)	Max. 10 ms (Approx. 5 ms)	
Reset time*	3 (at nominal voltage)	Max. 10 ms (Approx. 4 ms)	
Operate tim	e*3 (at nominal voltage)	Max. 10 ms (Approx. 5 ms)	
Release tim (at nominal	e(without diode)*³ voltage)	Max. 5 ms (Approx. 4 ms)	
Temperature	e rise	Max. 40°C (1a1b type) Max. 55°C (1a, 2a types)	
Soldering te	mperature	250°C (10 s) 300°C (5 s), 350°C (3 s)	
Shock	Functional*4	Min. 196 m/s ² {20 G}	
resistance	Destructive*5	Min. 980 m/s ² {100 G}	
Vibration	Functional*6	117.6 m/s ² {12 G}, 10 to 55 Hz at double amplitude of 2 mm	
resistance	Destructive	205.8 m/s ² {21 G}, 10 to 55 Hz at double amplitude of 3.5 mm	
Conditions for operation, transport and storage ^{*7} (Not freezing and condensing at low temperature)		−40°C to +65°C − 40°F 149°F	
Unit weight		Approx. 4.3 g .15 oz	

About Cd-free contacts

products to reduce environmentally hazardous substances. Please replace parts that contain cadmium with Cd-free products. Evaluate them with your actual application before use because the life of a relay depends on the contact material and load.

We have introduced cadmium-free type

Note: Add the suffix "F" to the part number for the 1 Form A 1 Form B contact type. The 1 Form A and 2 Form A contact types were originally Cd-free, hence the suffix "F" is not required.

TYPICAL APPLICATIONS

Office and industrial electronic devices

• Terminal devices of information

processing equipment, such as printer, data recorder.

- Office equipment (copier, facsimile)
- Measuring instruments
- NC machines, temperature controllers and programmable logic controllers.

ORDERING INFORMATION

Ex. DSP		- DC12V -	— R —	- F
Contact arrangement	Operating function	Coil voltage	Polarity	Contact material
1: 1a1b 1a: 1a 2a: 2a	Nil: Single side stable L: 1 coil latching L2: 2 coil latching	DC: 3, 5, 6, 9, 12, 24 V	Nil: Standard polarity R: Reverse polarity	● AgSnO₂ type F: 1a1b Nil: 1a, 2a

(Notes) 1. Standard packing: Carton: 50 pcs.; Case: 500 pcs.

UL/CSA, VDE approved type is standard.

2. Please inquire about the previous products (parts containing cadmium). (1 Form A 1 Form B type only)

TYPES AND COIL DATA (at 20°C 68°F)

Single side stable

Туре	Part No.	Nominal voltage, V DC	Pick-up voltage, V DC (max.)	Drop-out voltage, V DC (min.)	Nominal operating current, mA	Nominal operating power, mW	Coil resistance, Ω (±10%)	Max. allowable voltage, at 50°C, V DC
Single	DSPQ-DC3V (-F)	3	2.4	0.3	100	300	30	3.9
	DSPQ-DC5V (-F)	5	4.0	0.5	60	300	83	6.5
	DSPQ-DC6V (-F)	6	4.8	0.6	50	300	120	7.8
side stable	DSPQ-DC9V (-F)	9	7.2	0.9	33.3	300	270	11.7
ciab.c	DSPQ-DC12V (-F)	12	9.6	1.2	25	300	480	15.6
	DSPQ-DC24V (-F)	24	19.2	2.4	12.5	300	1,920	31.2

1 coil latching


Туре	Part No.	Nominal voltage, V DC	Pick-up voltage, V DC (max.)	Reset voltage, V DC (max.)	Nominal operating current, mA	Nominal operating power, mW	Coil resistance, Ω (±10%)	Max. allowable voltage, at 50°C, V DC
	DSPQ-L-DC3V	3	2.4	2.4	50	150	60	3.9
	DSPQ-L-DC5V	5	4.0	4.0	30	150	167	6.5
1 coil	DSPQ-L-DC6V	6	4.8	4.8	25	150	240	7.8
latching	DSPQ-L-DC9V	9	7.2	7.2	16.7	150	540	11.7
	DSPQ-L-DC12V	12	9.6	9.6	12.5	150	960	15.6
	DSPQ-L-DC24V	24	19.2	19.2	6.3	150	3,840	31.2

2 coil latching

Туре	Part No.	Nominal voltage, V DC	Set voltage, V DC (max.)	Reset voltage, V DC (max.)	Nominal operating current, mA	Nominal operating power, mW	Coil resistance, Ω (±10%)	Max. allowable voltage, at 50°C, V DC
	DSPQ-L2-DC3V (-F)	3	2.4	2.4	100	300	30	3.9
	DSPQ-L2-DC5V (-F)	5	4.0	4.0	60	300	83	6.5
	DSPQ-L2-DC6V (-F)	6	4.8	4.8	50	300	120	7.8
	DSPQ-L2-DC9V (-F)	9	7.2	7.2	33.3	300	270	11.7
	DSPQ-L2-DC12V (-F)	12	9.6	9.6	25.5	300	480	15.6
	DSPQ-L2-DC24V (-F)	24	19.2	19.2	12.5	300	1,920	31.2

Notes: 1. Insert 1a, 1 or 2a in, 2 Gor contact form required. 2. The Suffix "F" is required only for DSP1-.

DIMENSIONS




10


50 20


(Reset condition)


(Deenergized condition)


DSP **REFERENCE DATA**











10

Min Min

120

Drop-out

-voltage

°C

Pick-up voltage 14

Ambient mperature

Operate time

5.-(3) Change of pick-up and drop-out voltage

50

20 40 60 80

-50


Rate of change

Roloaso time

100


- Coil applied voltage, %V

4.-(4) Operate & release time (with diode, 1a type) Sample: DSP1a-DC12V, 5 pcs.





5.-(1) Change of pick-up and drop-out voltage (1a type)

Sample: DSP1a-DC12V, 5 pcs.



6.-(1) Influence of adjacent mounting (1a type)







NOTES

Soldering should be done under the following conditions: 250°C 482°F within 10 s $300^{\circ}C 572^{\circ}F$ within 5 s 350°C 662°F within 3 s


4.-(5) Operate & release time (with diode, 1a1b type) Sample: DSP1-DC12V, 5 pcs.



5.-(2) Change of pick-up and drop-out voltage (1a1b type) Sample: DSP1-DC12V, 5 pcs.



6.-(2) Influence of adjacent mounting (1a1b type) Sample: DSP1-DC12V, 5 pcs.



6.-(3) Influence of adjacent mounting (2a type)

Sample: DSP2a-DC12V, 5 pcs.

4.-(6) Operate & release time

Sample: DSP2a-DC12V, 5 pcs.

(with diode, 2a type)

шs

time,


Operate & release

(2a type)

0


80

Sample: DSP2a-DC12V, 5 pcs.



For Cautions for Use, see Relay Technical Information.


DSP SOCKETS FOR DSP RELAYS



SPECIFICATIONS


Item	Specifications
Breakdown voltage	3,000 Vrms between terminals (Except for the portion between coil terminals)
Insulation resistance	1,000 M Ω between terminals at 500 V
Heat resistance	150°C for 1 hour
Max. continuous current	1a: 8 A 2a: 5 A

DIMENSIONS




TYPES AND APPLICABLE RELAYS

Туре	No. For E)SP1a	For DSP1a, DSP1, DSP2a		
Applicable relays	DSP1a-PS	DSP1a-PSL2	DSP2a-PS	DSP2a-PSL2	
DSP1a relays	OK	OK	OK	OK	
DSP1a-L2 relays		OK		OK	
DSP1 relays			OK	OK	
DSP1-L2 relays				OK	
DSP2a relays			OK	OK	
DSP2a-L2 relays				OK	



Terminal No.2 and 15 are for DSP1a-PSL2 only.

PC board pattern (Copper-side view)



mm inch


Terminal No.2 and 15 are for DSP2a-PSL2 only.

FIXING AND REMOVAL METHOD

1. Match the direction of relay and socket.



2. Both ends of relays are fixed so surely that the socket hooks on the top surface of relays.



Good

No good

3. Remove the relay, applying force in the direction shown below.



4. In case there is not enough space for finger to pick relay up, use screw drivers in the way shown below.

