

REV.	MODIFICATION.	DATE	DRN
01	NEW DRAWING	30/05/06	NJB
02	CO2010295	23/07/08	SF
03	CO2010851	19/11/09	TC
04	CO2010863	14/12/09	TC

Fig 1.

Fig 2.

Fig 3.

Fig 4.

Fig 5.

Fig 6.

Ferrite Mat'l: K5B • Casing Mat'l: Black Nylon 6/6, RMS-244 •										
RRC	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)	Impedance (Ω)		Fig.	Applicable Cable Max. (mm)	Standard Pack (Pieces)
						25MHz	100MHz			
RRC-10-5-20-M-K5B	13.00	25.50	5.00	12.00	2.40	93	158	3	3.5	60
RRC-20-5-30-M-K5B	23.00	36.00	5.00	22.00	10.00	270	560	5	4-1.5	80
RRC-12-7-15-M-K5B	14.00	22.00	7.00	18.00	15.50	47	101	2	7	150
RRC-13-7-23-M-K5B	17.00	30.00	7.00	15.00	3.00	115	180	3	4	36
RRC-16-8-13-M-K5B	19.50	23.00	8.00	17.00	23.00	60	120	1	8	80
RRC-16-8-16-M-K5B	19.50	23.40	8.20	20.00	26.10	75	160	1	8	40
RRC-14-7-28-M-K5B	20.00	39.00	8.50	20.00	N/A	150	260	4	7	80
RRC-17-9-28-K5B	17.50	28.50	9.50	1.30	N/A	97	207	6	9	100
RRC-16-8-28-M-K5B	19.50	36.00	9.50	18.00	6.50	130	200	3	8	50
RRC-16-9-28-M1-K5B	19.50	35.00	9.50	31.00	20.00	120	190	2	9	50
RRC-16-9-28-M2-K5B	20.00	36.00	9.50	18.00	6.50	120	190	3	9	50
RRC-20-10-10-M-K5B	24.50	28.50	10.20	13.50	20.00	50	105	1	10	44
RRC-17-11-28-M-K5B	20.50	36.00	11.00	31.50	20.50	98	160	2	11	50
RRC-24-11-14-M-K5B	28.00	31.50	11.50	18.00	24.00	70	140	1	11.5	40
RRC-26-13-30-M-K5B	30.75	39.00	13.00	34.00	31.00	140	225	2	13	20
RRC-20-13-30-M-K5B	23.00	36.00	13.50	22.00	10.00	90	140	3	12	80
RRC-25-15-12-M-K5B	29.00	33.00	15.00	15.50	21.50	45	100	1	15	36
RRC-35-23-15-K5B	35.50	15.00	23.00	17.40	N/A	51	108	6	22	48

Standard Pack sizes may vary

- NOTES.
- 1) See drawing 05-126 sheets 2 & 3 of 3 for Impedance graphs.
 - 2) Impedance figures are typical values.
 - 3) Other sizes available by special order.
 - 4) Packaging information is only a guide & subject to variation.

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.

ALL DIMENSIONS IN MM
GENERAL TOLERANCES ±0.25
UNLESS OTHERWISE STATED
1 DECIMAL PLACE ±
2 DECIMAL PLACES ±
ANGULAR ±1°

THIRD ANGLE











MATERIAL: See Table
COLOUR: See Table

DESCRIPTION: RRC Split Ferrite Cores With Plastic Casings.
PART No: See Table

DRG No: 05-126
NPR No:
Mass:(g) SHEET SIZE A3

DRN DATE CHKD DATE SCALE SHEET No.
NJB 31/10/05 AS 30/05/06 NTS 1 OF 3

REV.	MODIFICATION.	DATE	DRN
01	NEW DRAWING	30/05/06	NJB



NOTES.
1) Impedance figures are typical values.

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.











DESCRIPTION:
RRC Split Ferrite Cores With Plastic Casing, Impedance Graphs.

DRG No: 05-126 SHEET SIZE A3

DRN	DATE	CHKD	DATE	SCALE	SHEET No.
NJB	30/05/06	AS	30/05/06	NTS	2 OF 3

REV.	MODIFICATION.	DATE	DRN
01	NEW DRAWING	30/05/06	NJB



NOTES.
1) Impedance figures are typical values.

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.



DESCRIPTION:
RRC Split Ferrite Cores With Plastic Casing, Impedance Graphs.

DRG No: 05-126		SHEET SIZE A3	
DRN NJB	DATE 30/05/06	CHKD AS	DATE 30/05/06
SCALE NTS		SHEET No. 3 OF 3	