






	Relay with 1 changeover contact and status indication (Relay height: 15 mm) Nominal input voltage V_N 24 V, 115 V, 230 V AC	Relay with 2 changeover contact and status indication (Relay height: 15 mm) Nominal input voltage V_N AC 24 V, 115 V, 230 V
--	---	---



Load limit curve for 788-311 to 788-315, 788-512, 788-515 and 788-516



Description	V_N	I_N	Item No.	Pack. unit	V_N	I_N	Item No.	Pack. unit
Relay sockets with pluggable miniature switching relay, for DIN 35 rail	24 V AC	34 mA	788-506	1	24 V AC	34 mA	788-512	1
	115 V AC	8 mA	788-507	1	115 V AC	8 mA	788-515	1
	230 V AC	4.3 mA	788-508	1	230 V AC	3 mA	788-516	1

Technical Data

Accessories see pages 74 ... 77 + 80 ... 81

Accessories see pages 74 ... 77 + 80 ... 81

Contact material	AgNi 90/10	
Input voltage range	$V_N \pm 10\%$	
Max. switching voltage	250 V AC	
Max. continuous current	16 A	
Max. make current (resistive) at a 10 % duty cycle	4 s 30 A (AC)	
Max. Switching power (resistive)	4 kVA AC, DC see load limit curve	
Max. switching rate with / without load	6 min ⁻¹ / 1200 min ⁻¹	
Operating power	0.75 VA	
Pull-in/drop-out/bounce time typ.	7 ms / 3 ms / 3 ms	
Nominal operating mode	continuous duty	
Dielectric strength contact-coil	5 kV	
Dielectric strength open contact	1 kV	
Nominal voltage acc. to VDE 0110 Part 1/4.97, IEC 60664-1	250 V / 4 kV / 3	
Mechanical life	10 x 10 ⁶ switching operations	
Degree of protection	IP20	
Ambient operating temperature	-25 °C ... +50 °C	
Storage temperature	-40 °C ... +70 °C	
Dimensions (mm) W x H x L	15 x 54 x 86	
Wire connection	Height from upper-edge of DIN 35 rail CAGE CLAMP®S	
Cross sections	0.34 mm ² ... 2.5 mm ² / AWG 22 ... 12	
Stripped lengths	9 ... 10 mm / 0.37 in	
Approvals	DIN VDE 0140 part 1, DIN EN 61140; DIN VDE 0160, EN 50178; degree of protection II; Ⓢ; UL 508	