



Sockets with Solid State Relay

Solid state relay
Input: 24 V DC
Output: 0 V ... 24 V DC / 3.5 A

Solid state relay
Input: 24 V DC
Output: 0 V ... 24 V DC / 5 A



Description	Item No.	Pack. unit	Item No.	Pack. unit
Relay socket with solid state relay, for DIN 35 rail	788-700	1	788-701	1
Technical Data	Accessories see pages 80 ... 81		Accessories see pages 80 ... 81	
Control circuit:				
Nominal input voltage (V_N)	24 V DC		24 V DC	
Input voltage range	18 V ... 30 V DC		15 V ... 30 V DC	
Control current U_N (20°C)	7 mA ±10 %		9.3 mA ±10 %	
Release voltage	8 V DC		2.5 V DC	
Control circuit resistance	3.2 kΩ		2.1 kΩ	
Load circuit:				
Load switching voltage range	0 ... 24 V DC		0 ... 30 V DC	
Peak reverse voltage	33 V		36 V	
Max. switching current	3.5 A DC		DC12/DC13 (5 A DC)	
Min. switching current			1 mA DC	
Pull-in time			50 µs	
Drop-out time			600 µs	
Switching frequency (max.)			100 Hz at 5 A	
Forward voltage at max. switching current	< 0.1 V DC		0.3 V DC	
Nominal operating mode	continuous duty		continuous duty	
Dielectric strength control/switching circuit	2.5 kV		2.5 kV	
Nominal voltage acc. to VDE 0110 Part 1/4.97, IEC 60664-1	250 V / 2.5 kV / 2		250 V / 2.5 kV / 2	
Degree of protection	IP 20		IP 20	
Ambient operating temperature	-20 °C ... +60 °C		-40 °C ... +60 °C	
Storage temperature	-40 °C ... +70 °C		-40 °C ... +70 °C	
Dimensions (mm) W x H x L	15 x 53 x 86		15 x 63 x 86	
Wire connection	Height from upper-edge of DIN 35 rail CAGE CLAMP®S		Height from upper-edge of DIN 35 rail CAGE CLAMP®S	
Cross sections	0.34 mm² ... 2.5 mm² / AWG 22 ... 12		0.34 mm² ... 2.5 mm² / AWG 22 ... 12	
Stripped lengths	9 ... 10 mm / 0.37 in		9 ... 10 mm / 0.37 in	
Approvals	DIN VDE 0140 part 1, DIN EN 61140; DIN VDE 0160, EN 50178; degree of protection II		DIN VDE 0140 part 1, DIN EN 61140; DIN VDE 0160, EN 50178; degree of protection II	