



COMPACT SIZE AUTOMOTIVE RELAY


JJ-M RELAYS

FEATURES

• Compact (half-size).

The base area is approximately half the size of conventional (JS-M) relays. The controller unit can be made more compact.

Base area has been reduced by one half



· Perfect for automobile electrical systems.

Over 2 × 10⁵ openings possible with a 14 V DC motor load, an inrush current of 25 A, and steady state current of 5 A. (N.O. side)

Standard terminal pitch employed

The terminal array used is identical to that used in small automotive relays.

Plastic sealed type.

Plastically sealed for automatic cleaning.

• Line-up of 1 Form A and 1 Form C.

TYPICAL APPLICATIONS

- Power windows
- Auto door lock
- · Electrically powered sun roof
- Electrically powered mirror
- · Cornerring lamp, etc.

SPECIFICATIONS

Contact

eentaet					
Arrangement			1 Form A	1 Form C	
Contact material			AgSnO ₂ type		
Initial contact resistance (By voltage drop 6V DC 1A)			Max. 100 mΩ		
Rating (resistive load)	Nominal switching capacity		20 A 14 V DC	20 A 14 V DC (N.O.) 10 A 14 V DC (N.C.)	
	Min. switching capacity ^{#1}		1 A 12 V DC		
	Max. carrying current		35 A (12V, at 20°C 68°F for 2 minutes) 25 A (12V, at 20°C 68°F for 1 hour) 30 A (12V, at 85°C 185°F for 2 minutes) 20 A (12V, at 85°C 185°F for 1 hour)		
	Mechanical (at 120cpm)		107		
Expected life (min. operations)	Electrical (at rated load)	Resistive	105 *1	10 ⁵ (N.O.)* ² 10 ⁵ (N.C.)* ³	
		Motor load	2×10 ^{5 *4} 5×10 ^{4 *5}	2×10 ⁵ (N.O.)*6 5×10 ⁴ (N.O.)*7 2×10 ⁵ (N.C.)*8	
Coil	1	1	1	<u> </u>	

mm inch

Coil

Nominal operating power

#1 This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.

640 mW

Remarks

- *1 at 20 A 14 V DC, at 20 cpm, operating frequency: 1s ON, 9s OFF
 *2 at 20 A 14 V DC, operating frequency: 1s ON, 9s OFF
 *3 at 10 A 14 V DC, at 20 cpm, operating frequency: 1s ON, 9s OFF

- *4 at 5 A (steady), 25 A (inrush) 14 V DC
- *5 at 20 A 14 V DC (Motor lock), operating frequency: 0.5 s ON, 9.5 s OFF $^{\ast 6}~$ at 5A (steady), 25 A (inrush) 14 V DC

Characteristics

enaraeterietiee				
Max. operating sp	6 cpm			
Initial insulation re	Min. 100 MΩ (at 500 V DC)			
Initial breakdown	Between open contacts		500 Vrms for 1min.	
voltage*10	Between c	contact and coil	500 Vrms for 1min.	
Operate time*11 (at nominal voltage)			Max. 10 ms (at 20°C 68°F)	
Release time (without diode)*11 (at nominal voltage) (Initial)			Max. 10 ms (at 20°C 68°F)	
Shock resistance		Functional*12	Min. 100 m/s ² {10 G}	
		Destructive*13	Min. 1,000 m/s ² {100 G}	
Vibration resistance		Functional*14	10 Hz to 100 Hz, Min. 44.1 m/s² {4.5 G}	
		Destructive*15	10 Hz to 500 Hz, Min. 44.1 m/s² {4.5 G}	
Conditions in case of opera- tion, transport and storage ^{*16} (Not freezing and condens- ing at low temperature)		Ambient temp.	−40°C to +85°C −40°F to +185°F	
		Humidity	5% R.H. to 85% R.H.	
Mass			Approx. 5 g .176 oz	

*7 at 20 A 14 V DC (Motor lock)

*8 at peak 20 A 14 V DC (Braking current) operating frequency: 0.5 s ON, 9.5 s OFF

Measurement at same location as "Initial break down voltage" section. *10 Detection current: 10mA

*11 Excluding contact bounce time.

 *12 Half-wave pulse of sine wave: 11 ms; detection time: 10 μs

*13 Half-wave pulse of sine wave: 6 ms

*14 Detection time: 10 μs


*15 Time of vibration for each direction; X, Y, Z direction: 2 hours



*16Refer to 6. Conditions for operation, transport and storage mentioned in AMBIENT ENVIRONMENT (p. 19, Relay Technical Information).

ORDERING INFORMATION

JJ-M



(Note) Standard packing: Carton: 50 pcs.; Case: 1,000 pcs.


TYPES AND COIL DATA (at 20°C 68°F)

			-	•				
Contact arrangement	Part No.	Nominal voltage, V DC	Pick-up voltage, V DC (Initial)	Drop-out voltage, V DC (Initial)	Coil resistance Ω	Nominal operating current mA	Nominal operating power mW	Usable voltage range, V DC
1 Form A	JJM1a-12 V	12	Max. 7.2	Min. 1.0	225±10%	53.3±10%	640	10 to 16
1 Form C	JJM1-12 V	12	Max. 7.2	Min. 1.0	225±10%	53.3±10%	640	10 to 16

* Other pick-up voltage types are also available. Please contact us for details.

DIMENSIONS






Note: *Marked terminal is only for 1Form C type

* Dimensions (thickness and width) of terminal specified in this catalog is measured before pre-soldering.


Intervals between terminals is measured at A surface level.

Dimension:	General tolerance
Max. 1mm .039 inch:	±0.1 ±.004
1 to 3mm .039 to .118 inch:	$\pm 0.2 \pm .008$
Min. 3mm .118 inch:	±0.3 ±.012

REFERENCE DATA








Schematic (Bottom view) 1a






mm inch




1c




Tolerance: ±0.1 ±.004

3. Ambient temperature and operating voltage range



ds_61210_0001_en_jjm: 061006J


4. Distribution of pick-up and drop-out voltage Sample: JJM1-12V, 100pcs



7-(1). Electrical life test (at rated load) Sample: JJM1-12V


Quantity: n = 6 (NC = 3, NO = 3)

Load: Resisitive load (NC side: 10A 14 V DC, NO side: 20 A 14 V DC); Operating frequency: ON 1s, OFF 9s Ambient temperature: Room temperature




7-(2). Electrical life test (Motor free) Sample: JJM1-12V, 6pcs. Load: 5A, Inrush 25A, Brake current 18A 14V DC, Power window motor load (Free condition). Operating frequency: (ON : OFF = 0.5s : 9.5s) Ambient temperature: Room temperature

Circuit :





7-(3). Electrical life test (Motor lock) Sample: JJM1-12V, 6pcs. Load: 20A, 14VDC, Power window motor actual load (lock condition).

Operating frequency: (ON : OFF = 1s : 5s) Ambient temperature: Room temperature



5. Distribution of operate time Sample: JJM1-12V, 100pcs





Change of pick-up and drop-out voltage

Pick-up voltage

Drop-out voltage

5

No. of operations, × 104

Contact welding: 0 time Miscontact: 0 time

Max

Min.

Max X Min.

10

8

7

6

5

4

3


2


0


>

Pick-up and drop-out voltage,











Change of contact resistance





7-(4). Electrical life test (Lamp load) Sample: JJM1-12V, 6pcs. Load: 27W+21W, min. 4A (steady), Lamp actual load Operating frequency: ON 2s, OFF 13s Ambient temperature: Room temperature

Circuit :




Inrush current: 42A, Steady current: 4.4A





Change of pick-up and drop-out voltage



Change of contact resistance

For Cautions for Use, see Relay Technical Information.