finder

70 Series - Line monitoring relay

1

Features	70.1 1	70.31	70.41
Electronic voltage monitoring relays for	10 to 100	CCC.	8 886
 single and three-phase applications Multifunctional types, providing the flexibility of monitoring Undervoltage, Overvoltage, Window Mode, Phase rotation, Phase loss, Asymmetry and Neutral loss Positive safety logic - Make output contact opens if the relay detects an error All functions and values can be easily adjusted 			
 by the selector and trimmer on front face "Blade + cross" – both flat blade and cross head screw drivers can be used to adjust the 	Single-phase (220240 V) voltage monitoring:	Three-phase (380415 V) voltage monitoring:	Three-phase (380415 V, with or without neutral)
 regulators and the function selector Colored LEDs for clear & immediate visual indication 1 CO relay output, 6 or 10 A Modular housing, 17.5 or 35 mm wide 35 mm rail (EN 60715) mount Cd-free contact material 	 Undervoltage Overvoltage Window mode (overvoltage + undervoltage) Voltage fault memory selectable 	 Undervoltage Overvoltage Window mode (overvoltage + undervoltage) Voltage fault memory selectable Phase loss Phase rotation 	voltage monitoring: • Window mode (overvoltage + undervoltage) • Phase loss • Phase rotation • Asymmetry • Neutral loss selectable
Screw terminal			
For outline drawing see page 8			
Contact specification			
Contact configuration	1 CO (SPDT)	1 CO (SPDT)	1 CO (SPDT)
Rated current/Maximum peak current A Rated voltage/Max. switching voltage VAC	10 / 30	6 / 10	6 / 10 250 / 400
Rated voltage/Max. switching voltage VAC Rated load AC1 VA	250 / 400 2,500	250 / 400	1,500
Rated load AC1 VA	750	500	500
Single phase motor rating (230 V AC) kW	0.5	0.185	0.185
Breaking capacity DC1: 30/110/220 V AC	10 / 0.3 / 0.12	6 / 0.2 / 0.12	6 / 0.2 / 0.12
Minimum switching load mW (V/mA)		500 (12 / 10)	500 (12 / 10)
Standard contact material	AgNi	AgNi	AgNi
Supply specification	Agiti	, Agi ti	Agiti
Nominal system voltage (U _N) V AC (50/60 Hz)	220240	380415	380415
Rated power VA (50 Hz) / W		11 / 0.9	11/ 0.9
Operating range V AC (50/60 Hz)		220510	220510
Technical data			
Electrical life at rated load AC1 cycles	80 · 10 ³	60 · 10 ³	60 · 10 ³
Voltage detection level range V		300480	300480
Asymmetry detection level range %		_	425
Switch-off delay time (T on function diagrams) s	0.560	0.560	0.560
Switch-on lock-out time s	0.5	1	1
Switch-on hysteresis (H on function diagrams) V	5 (L-N)	10 (L-L)	10 (L-L)
Power-on activation time s	1	≈ 1	≈ 1
Insulation between supply and contacts (1.2/50 µs) kV	4	4	4
Dielectric strength between open contacts V AC	1,000	1,000	1,000
Ambient temperature °C	-20+50	-20+50	-20+50
Protection category	IP20	IP20	IP20
Approvals (according to type)		(6 🚱	·

Inder

Features

Electronic phase loss and rotation monitoring relay for three-phase applications

- Universal voltage monitoring (U_N from 208 V to 480 V, 50/60 Hz)
- Phase loss monitoring, even under phase regeneration
- Positive safety logic Make contact opens if the relay detects an error
- 1 CO relay output, 6 A
- Compact size (17.5 mm wide)
- 35 mm rail (EN 60715) mount

For outline drawing see page 8

Rated current/Maximum peak current

Rated voltage/Max. switching voltage

Single phase motor rating (230 V AC)

Breaking capacity DC1: 30/110/220 V

Nominal system voltage (U_N) V AC (50/60 Hz)

Insulation between supply and contacts (1.2/50 $\mu s)$ kV Dielectric strength between open contacts V AC

Contact specification

Contact configuration

Rated load AC1

Rated load AC15

Minimum switching load

Supply specification

Rated power

Operating range Technical data

Switch-off delay time

Switch-on lock-out time

Ambient temperature

Approvals (according to type)

Protection category

Power-on activation time

Standard contact material

Electrical life at rated load AC1

• European patent pending for the innovative principle at the root of the 3 phase monitoring . Phase loss and error survey system







Three-phase (208...480 V) voltage monitoring:

1 CO (SPDT)

6/15

250 / 400

1,500

250

0.185

3 / 0.35 / 0.2

500 (10 / 5)

AgCdO

208...480

8/1

170...500

100 · 10³

0.5

0.5

< 2

5

1,000

-20...+50

IP20

c**A**[®]us

CE @

A

V AC

VA

VA

kW

mW (V/mA)

VA (50 Hz) / W

V AC (50/60 Hz)

cycles

s

s

s

°C


A

70 Series - Line monitoring relay



Ordering information

Example: 70 series, three-phase voltage monitoring relay, 1 output , supply voltage 380...415 V AC.



Monitoring and function overview

	70.11	70.31	70.41	70.61
Supply system type	Single phase system	3-phase systems	3-phase systems	3-phase systems
Nominal voltage 50/60 Hz V	220240	380415	380415	208480
Undervoltage with/without memory (selectable)	•	•	_	_
Overvoltage with/without memory (selectable)	•	•	_	_
Window Mode with/without memory (selectable)	•	•	_	_
Window Mode without memory	_	_	•	_
Phase loss	_	•	•	•
Phase rotation	-	•	•	•
Phase asymmetry	_	_	•	_
Neutral loss selectable	_	_	•	_


Technical data

Insulation			70.11/31/41		70.61		
Between supply and contacts	dielectric strength V		2,500		3,000		
	impulse (1.2/50 µs)	kV	4		5		
Between open contacts	dielectric strength	V AC	1,000		1,000		
	impulse (1.2/50 µs)	kV	1.5		1.5		
EMC specifications							
			Reference standard				
Electrostatic discharge	contact discharge		EN 61000-4-2		4 kV		
	air discharge		EN 61000-4-2		8 kV		
Radiated electromagnetic field	80 1,000 MHz		EN 61000-4-3		10 V/m		
	1 2.8 GHz		EN 61000-4-3		5 V/m		
Fast transients	on supply terminals		EN 61000-4-4		4 kV	4 kV	
(burst 5/50 ns, 5 and 100 kHz)							
Voltage pulses on supply	common mode		EN 61000-4-5		4 kV		
terminals (surge 1.2/50 µs)	differential mode		EN 61000-4-5		4 kV		
Radiofrequency common mode	on supply terminals		EN 61000-4-6		10 V		
voltage (0.15230 MHz)							
Voltage dips	70 % U _N		EN 61000-4-11		25 cycles		
Short interruptions			EN 61000-4-11		1 cycle		
Radiofrequency conducted emissions	0.1530 MHz		CISPR 11		class B		
Radiated emissions	301,000 MHz		CISPR 11		class B		
Terminals			solid cable		-	tranded cable	
Max. wire size mm ²		mm ²	1 x 6 / 2 x 4		1 x 4 / 2 x 2.5		
		AWG	1 x 10 / 2 x 12		1	x 12 / 2 x 14	
Screw torque		Nm	0.8				
Wire strip length		mm	9				
Other data			70.11	70.3	81/41	70.61	
Power lost to the environment	without output current	W	0.8	-).9	1	
	with rated output current	W	2	1	.2	1.4	



Functions

Output relay On (NO closed) when all OK: positive logic.



Functions

— = Output contact (11-14)
 OV = Overvoltage
 OVm = Overvoltage with memory
 UV = Undervoltage with memory
 UVm = Undervoltage with memory
 W = Window mode (OV + UV)
 Wm = Window mode (OV + UV)
 with memory
 H = Hysteresis

If the voltage moves out of limits, following delay **T** the output relay turns Off.


When the voltage is again within limits (± the Switch-on hysteresis **H**):

- if set in the "without memory" position, the output relay "recovers", i.e. it turns On (after the Switch-on lock-out time) without any memory of the previous event.
- if set in the "with memory" position (70.11 and 70.31 only), the output relay remains open. To reset, it is necessary to switch the supply Off and then On again, or to rotate the selector first to an adjacent position and then to the original position.




Functions

Output relay On (NO closed) when all OK: positive logic.





Front view: function selector and regulators



LED indication

Monitoring relay Type	LED	Supply system normal	Supply system abnormal (Voltage out of limits, switch-off delay time T running)	Supply system abnormal (Reason for switch-off, RESET necessary when"with Memory"* is selected)		
		Contact 11 - 14 closed	Contact 11 - 14 closed	Contact	11-14 open	
	•				Overvoltage OV and OVm	
70.11.8.230.2022	•				Undervoltage UV and UVm	
					With Memory, following a failure a manual "RESET" ** is necessary	
	•				Overvoltage OV and OVm	
70.31.8.400.2022	•				Undervoltage UV and UVn	
	•				Phase loss	
				111 111 111	Phase rotation	
					With Memory, following a failure a manual "RESET" ** is necessary	
	•				Overvoltage OV	
70.41.8.400.2030	•				Undervoltage UV	
	•				Asymmetry	
				1 1 1	Phase loss	
				11 11 11	Neutral loss	
				111 111 111	Phase rotation	
70.61.8.400.0000	•				Phase rotation or Phase loss	


* The function "with Memory" is only available for type 70.11 and 70.31.

** It is necessary to switch the supply OFF and then On again (U off U on) or to rotate the function selector first to an adjacent position and then to the original position.




70 Series - Line monitoring relay

Wiring diagrams




Application example The output contact switches the coil of the line contactor.




finder


70 Series - Line monitoring relay

Outline drawings







70.61




70.41 Screw terminal



IJ









70 Series - Line monitoring relay

011.01

Accessories



Adaptor for panel mounting, plastic, 17.5 mm wide for 70.11 and 70.61	020.01



011.01

Adaptor for panel mounting, plastic, 35 mm wide for 70.31 and 70.41



Sheet of marker tags, plastic, 72 tags, 6x12 mm for 70.11, 70.31 and 70.41 060.72

060.72

•	1	11	T	1	T	T	ľ
•	i		1	Ť	1	1	
•	T	T	Т	Ť	T	T	
•		1	T	-i-	1	1	
-							

Sheet of marker tags, plastic, 24 tags, 9x17 mm for 70.61	020.24

020.24



Identification tag, plastic, 1 tag, 17x25.5 mm for 70.11, 70.31 and 70.41	019.01
---	--------

019.01



020.03

