

Adapter cable - CABLE-20/8/250/RSM/FANUC - 2986999

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable adapter for PSR speed monitors (PSR-RSM4 and PSR-MOTIONSTOP), cable length: 2.5 m, for controller: FANUC CN

Product Features

- Option to connect to PSR-RSM4 and PSR-MOTIONSTOP safe speed monitors
- Suitable for connection to the existing motor feedback interface of an electrical drive
- Controller type: GE FANUC
- FANUC connectors
- Length of connecting cable to speed monitor: 250 cm

Key commercial data

package_quantity	1
GTIN	4046356477215

Technical data

Dimensions

Fixed cable length	2.5 m
---------------------------	-------

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C (for fixed installation)
Ambient temperature (operation)	0 °C ... 50 °C (for flexible installation)
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Connection 1	To the device
Connection method	RJ45
Number of positions	8
Connection method	FANUC plug/FANUC socket
Number of positions	20
Cable resistance	≤ 260 Ω/km
Conductor material	Bare Cu litz wires
Shielding	Plastic-coated aluminum foil, tinned copper braided shield
Shielding	Soldering on D-SUB housing
Conductor cross section	0.48 mm ² (AWG 26)

Adapter cable - CABLE-20/8/250/RSM/FANUC - 2986999

classifications

eCl@ss

eCl@ss 4.0	27060307
eCl@ss 4.1	27060307
eCl@ss 5.0	27060307
eCl@ss 5.1	27060307
eCl@ss 6.0	27060307
eCl@ss 7.0	27060307
eCl@ss 8.0	27060307

ETIM

ETIM 3.0	EC000467
ETIM 4.0	EC000467
ETIM 5.0	EC000467

UNSPSC

UNSPSC 6.01	30211901
UNSPSC 7.0901	39121501
UNSPSC 11	39121501
UNSPSC 12.01	39121501
UNSPSC 13.2	39121501

Drawings