



QQGQ2.E214596
Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

Page Bottom

Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

See General Information for Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

PHOENIX CONTACT GMBH & CO KG

E214596

FLACHSMARKTSTRASSE 8

32825 BLOMBERG, GERMANY

Model No.	Rated Input			Max Output							
	Volts	Hz	SC	V	A	VA	OC	SP	EP	FC	GC
OPS1020.0, MINI-PS-100-240AC/24DC/2											
	100-240ac 90-350dc	50-60	0	28.1	5.2	91	3	60950	15B	5	2
5604601, 5604667											
	98-240ac	50-60	0	24dc	3	72	3	60950-1	15B	0	0
				240ac	6	1440	3				
MINI-PS-100-240AC/10-15DC/2											
	100-240ac 90-350dc	50-60	0	15dc	2	30	3	60950-1	15B	5	2
MINI-PS-100-240AC/12DC/2/SO1, 2866912											
	100-240ac 90-350dc	50-60	0	12dc	2	24	3	60950-1	15B	5	2
MINI-PS-100-240AC/2x15DC/1[*r]											
	100-240 ac or 90-350 dc	50-60	0,4	-15dc	1	-	3	60950	-	0	-
				15dc	1	-	3				
MINI-PS-100-240AC/5DC/3											
	100-240ac 90-350dc	50-60	0	5.6	6.2	28.5	3	60950	15b	5	2
OPS1025.2											
	100-240ac	50-60	-	24dc	2.5	-	-	-	-	-	-
OPS1042.2											
	100-240ac	50-60	-	24dc	4.2	-	-	-	-	-	-
STEP-DIODE/5-24DC/2x5/1x10											
	5-24dc	-	-	5-24dc	0-10	-	-	60950-1	-	-	-
STEP-PS/1AC/12DC/1[*r]											
	100-240ac	50-60	0	12dc	1	-	1	60950-1 2nd	20B	5	2
STEP-PS/1AC/12DC/1.5											
	100-240ac	50-60	0	12.1dc	2.2	22.3	0	60950-1	20B	5	2
STEP-PS/1AC/12DC/1.5/FL											

100-240ac	50-60	0	12.1dc	2.2	22.3	0	60950-1	20B	5	2
STEP-PS/1AC/12DC/3.0[*r]										
100-240 Vac / 95-250 Vdc	50-60	0	12dc	3	36	3	60950-1	20B	5	2
STEP-PS/1AC/12DC/5.0[*r]										
100-240 Vac; 95-250 Vdc	50-60	0	12dc	5	60	3	60950-1	20B	5	2
STEP-PS/1AC/15DC/4.0[*r]										
100-240 Vac; 95-250 Vdc	50-60	0	15dc	4	60	3	60950-1	20B	5	2
STEP-PS/1AC/24DC/0.5[*r]										
100-240ac	50-60	0	24dc	0.5	-	1	60950-1 2nd	20B	5	2
STEP-PS/1AC/24DC/0.75										
100-240 ac 95-250 dc	50-60	0	24dc	0.75	18	3	60950-1	20B	5	2
STEP-PS/1AC/24DC/0.75/FL[*r]										
100-240ac	50-60	0	24dc	0.75	-	3	60950-1	-	0	2
STEP-PS/1AC/24DC/1.75[*r]										
100-240 Vac / 95-250 Vdc	50-60	0	24dc	1.75	42	3	60950-1	20B	5	2
STEP-PS/1AC/24DC/2.5										
100-240 ac 95-250 dc	50-60	0	24dc	2.5	60	3	60950-1	20B	5	2
STEP-PS/1AC/24DC/3.8/C2LPS										
100-240 Vac, 95-250 Vdc	50-60	0	24dc	5.0	92.3	1	60950-1	20B	5	2
STEP-PS/1AC/24DC/4.2[*r]										
100-240 Vac; 95-250Vdc	50-60	0	24dc	4.2	100.8	3	60950-1	20B	5	2
STEP-PS/1AC/48DC/2										
100-240 Vac; 95-250 Vdc	50-60	0	48dc	2.0	96	3	60950-1	20B	5	2
STEP-PS/1AC/5DC/6.5[*r]										
100-240 Vac; 95-250 Vdc	50-60	0	5dc	6.5	32.5	3	60950-1	20B	5	2
STEP-PS/48AC/24DC/0.5[*r]										
48ac	50-60	0	24dc	0.5	-	1	60950-1 2nd	20B	5	2
STEP-UPS/24DC/24DC/3[*r]										
24dc	-	3	24dc	3 @ amb. 40°C	-	3	60950-1 2nd	-	5	-
			24dc	4 @ amb. 35°C	-	3				

[*r] - Output values are rated.

Marking: Company name and catalog designation on the product or on the smallest unit container in which the product is packaged.

Last Updated on 2012-05-09

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2012 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2012 UL LLC".