

Product Information

LC 100 - Level Controller 100

Tank contents indicator with remaining volume check



Tank contents measurement up to 9.999 litres

LC 100 is an electronic instrument for indication of tank contents in litres and percentage of tank volume. All common tank shapes are supported. The measurement is done contactless using 40 kHz ultrasonic pulses. The installation is very easy. LC 100 is maintenance free and highly reliable.

LC 100 is a direct replacement for the mechanical gauges.

Features

- Display of remaining empty tank volume
- Precise digital display
- Contact-less measurement
- Long battery lifetime
- Easy installation
- Multiple measurements for best stability

LC 100 evaluates the propagation time of ultra-sonic pulses to detect the fluid level in the tank. Thus mechanical ageing problems cannot arise. All tank forms in common use are supported like cubic, cylindrical tanks, in horizontal or vertical position. From this information the tank contents in litres is calculated, also the average demand per day and the remaining time period based on average demand is derived.

Applications:

Heating oil, water tanks, rainwater tanks, waste oil tanks, ...

LC 100 provides the following values:

- Tank contents in litres up to 9.999 litres
- Tank contents in percent of volume
- Remaining empty tank volume in litres – how many litres can be refuelled
- Distance to the fluid surface in cm
- Average demand in litres/day
- Remaining time period in days based on average demand

Product Information

LC 100 - Level Controller 100

Tank contents indicator with remaining volume check

- Technical specification**

Dimensions (w x d x h):	80 x 80 x 170 mm
Screw thread:	1.5 inch (6/4") and 2 inch
Weight (without batteries):	app. 220 g
Housing:	colour black, oil resistive
Protection:	IP 20 as per EN 60529
Display:	indoor usage only, in cellars, tank rooms etc. LC-display 51 mm x 35 mm, 2 lines with 4 digits, 12 and 14 mm high
Temperature range:	-10°C ... +45°C
Power supply:	4 alkaline batteries, type AA, 1.5 V
Battery life time:	app. 2 years, warning symbol for weak batteries

LC 100 is CE-marked and manufactured conform to ROHS requirements.

Measurement method:

Principle:	Ultra-sonic pulses, 40 kHz, pulse duration: 20 ms
Range:	20 cm ... 250 cm (distance to the fluid surface)
Uncertainty:	±1 cm

Installation: Screwing in into the tank thread
1.5 inch (6/4") and 2 inch

Standard mode:

Every 24 hours a measurement is taken, the tank contents in litres and volume percentage will be displayed thereafter.

Manual measurement mode:

A button press initiates a single measurement, tank content is displayed- afterwards the LC 100 falls back to power saving mode.




Power saving mode:

Display remains on permanently if the display shut-off function is deactivated.
Permanent display reduce battery lifetime!

Tank types: Type 1

Type 2

Type 3



Order reference:

LC 100 tank contents indicator

Order No.: ST001001

Scope of delivery:

LC 100, operating instructions,

DESIGN & DEVELOPMENT BY

