



# VOLTCRAFT®

## VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

“Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

# VSP 2410



# LABORATORY POWER SUPPLY UNIT

VERSION 12/21

Nº 51 19 19

The high developed switching power supply technology with active PFC allows stable output voltage and high efficiency. The output voltage can be set in series by using an external voltage and can be maintained independently from the load (scanning operation). A tracking function allows both the main outputs to be switched in series and in parallel. This means that the output voltage or current of an output can be doubled. Output A works as a master in parallel operation. The device has an additional 0 - 6 V / 1.5 A output for digital switching, amongst other items. The output current and voltage can be precisely set by using coarse and precision regulators. The C limit preset function allows current limiting to be set at the output without any short circuit bridges.

## HIGHLIGHTS

**Parallel / series or individual operation of the main outputs //**

**Switching power supply technology //**

**Can be remote controlled //**

**C limit preset function //**

**Scanning function //**



# GENERAL SPECIFICATIONS

**CONNECTIONS:** Outputs 4 mm grounded sockets, remote and scanning via screw terminals at the rear side **NUMBER OF OUTPUTS:** 3 **OUTPUT VOLTAGE 1:** 0.1 - 40 V/DC **OUTPUT VOLTAGE 2:** 0.1 - 40 V/DC **OUTPUT VOLTAGE 3:** 0.1 - 6 V/DC **INPUT VOLTAGE:** 230 V/AC **OUTPUT CURRENT 1:** 0 - 10 A **OUTPUT CURRENT 2:** 0 - 10 A **OUTPUT CURRENT 3:** 1.5 A **OUTPUT:** 809 W **WEIGHT:** 7.5 kg **DIMENSIONS (W x H x D):** 437 x 88 x 340 mm

## TECHNICAL DATA

Residual ripple at nominal load	
Output A of Vmax:	< 0.025 %
Output B of Vmax:	< 0.025 %
Output C of Vmax:	< 0.006 %
Voltage control response at 100 % load change:	< 0.04 % (Vmax)
Voltage control response at 20 % mains fluctuation:	< 0.005 % (Vmax)
Current control behaviour at 100 % load change:	< 5 mA
Current control behaviour at 20 % mains fluctuation:	< 5 mA
Operating voltage:	230 V/AC ( $\pm 20\%$ ), 47 - 53 Hz
Power consumption (max.):	1000 VA
Mains fuse:	slow blow (5 x 20 mm), T6.3A/250V
Operating temperature:	0 °C to +40 °C
Relative air humidity:	max. 80 %, non-condensing
Protection class:	1
Mains connection:	Low-power device installation plug, IEC 320 C14

## PACKAGE CONTENT

Laboratory power supply unit // Mains cable // Operating instructions

This data sheet is published by Voltcraft®, Lindenweg 15, D-92242 Hirschau / Germany, Phone +49 180 586 582 7. The data sheet reflects the current technical specifications at time of print. We reserve the right to change the technical or physical specifications.