



SIMATIC S7-300 STABILIZED POWER SUPPLY PS307
 INPUT: 120/230 V AC OUTPUT: DC 24 V DC/5 A

Technical specifications

Product	PS 307
Power supply, type	24 V/5 A
Input	
Input	1-phase AC
Supply voltage / 1 / at AC / nominal value	120 V
Supply voltage / 2 / at AC / nominal value	230 V
Voltage range	
• Note	Automatic range selection
Input voltage / 1 / at AC	85 ... 132 V
Input voltage / 2 / at AC	170 ... 264 V
Wide-range input	No
Overvoltage resistance	2.3 × Vin rated, 1.3 ms
Mains buffering at Iout rated, min.	20 ms
Mains buffering	at Vin = 93/187 V
Rated line frequency	50 / 60 Hz
Rated line range	47 ... 63 Hz
Input current / at nominal level of the input voltage 120 V	2.3 A
Input current / at nominal level of the input voltage 230 V	1.2 A
Switch-on current limiting (+25 °C), max.	20 A
Duration of current limiting / at 25 °C / maximum	3 ms


I ² t, max.	1.2 A ² ·s
Built-in incoming fuse	T 3,15 A/250 V (not accessible)
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 6 A, characteristic C
Output	
Output	Controlled, isolated DC voltage
Rated voltage V _{out} DC	24 V
Total tolerance, static ±	3 %
Static mains compensation, approx.	0.1 %
Static load balancing, approx.	0.5 %
Residual ripple peak-peak, max.	50 mV
Residual ripple peak-peak, typ.	10 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	150 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	20 mV
Product feature / output voltage adjustable	No
Output voltage setting	-
Status display	Green LED for 24 V OK
On/off behavior	No overshoot of V _{out} (soft start)
Startup delay, max.	2 s
Voltage rise, typ.	10 ms
Rated current value I _{out} rated	5 A
Current range	0 ... 5 A
delivered active power / typ.	120 W
short-term overload current / at short-circuit during run-up / typical	20 A
Duration of overloading ability for excess current / on short-circuiting during the start-up	100 ms
short-term overload current / at short-circuit during operation / typical	20 A
Duration of overloading ability for excess current / on short-circuiting during the operational phase	100 ms
Parallel switching for enhanced performance	Yes
Efficiency	
Efficiency at V _{out} rated, I _{out} rated, approx.	87 %
Power loss at V _{out} rated, I _{out} rated, approx.	18 W
Closed-loop control	
Dynamic mains compensation (V _{in} rated ±15 %), max.	0.1 %
Dynamic load smoothing (I _{out} : 50/100/50 %), U _{out} ± typ.	1 %
Load step setting time 50 to 100%, typ.	0.3 ms
Load step setting time 100 to 50%, typ.	0.3 ms
Protection and monitoring	
Output overvoltage protection	Additional control loop, shutdown at < 28.8 V, automatic restart
Current limitation	5.5 ... 6.5 A

Characteristic feature of the output / short-circuit protected	Yes
Short-circuit protection	Electronic shutdown, automatic restart
Enduring short circuit current / Effective level / maximum	7 A
Safety	
Primary/secondary isolation	Yes
Potential separation	Safety extra-low output voltage U _{out} acc. to EN 60950-1 and EN 50178
Protection class	Class I
stray current / maximum	3.5 mA
stray current / typical	0.5 mA
CE mark	Yes
UL/CSA approval	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 142), File E143289, UL 1604 Class I Div. 2 Group A, B, C, D, File E330455
Explosion protection	ATEX (EX) II 3G Ex nA II T4; UL 1604 Class I, Div. 2, Group ABCD
FM approval	Class I, Div. 2, Group ABCD, T4
CB approval	No
Marine approval	In S7-300 system
Degree of protection (EN 60529)	IP20
EMC	
Emitted interference	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2
Noise immunity	EN 61000-6-2
Operating data	
Ambient temperature / in operation	0 ... 60 °C
• Note	with natural convection
Ambient temperature / on transport	-40 ... +85 °C
Ambient temperature / in storage	-40 ... +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation
Mechanics	
Connection technology	screw-type terminals
Connections / Supply input	L, N, PE: 1 screw terminal each for 0.5 ... 2.5 mm ² single-core/finely stranded
Connections / Output	L+, M: 3 screw terminals each for 0.5 ... 2.5 mm ²
Connections / Auxiliary	-
Width / of the housing	60 mm
Height / of the housing	125 mm
Depth / of the housing	120 mm
Installation width	60 mm
Mounting height	205 mm

Weight, approx.	0.6 kg
Product feature / of the housing / housing for side-by-side mounting	Yes
Type of mounting / wall mounting	No
Type of fixing / cap rail mounting	No
Type of mounting / S7-300 rail mounting	Yes
Installation	Can be mounted onto S7 rail
Mechanical accessories	Mounting adapter for standard mounting rail (6EP1971-1BA00)

Other information

Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)



Dimensions are in millimeters (mm) unless otherwise specified.

letzte Änderung:

Sep 10, 2012