

AK 150

single

100~150W

Features :

- Green design, No-load power consumption < 0.5W
- Universal AC input / Full range
- Protections: Short circuit / Over load / Over voltage
Brown-out (Low AC Input voltage)
- Cooling by free air convection
- Power ON with LED indicator
- All using 105°C long life electrolytic capacitors
- High operation temperature up to 70° C
- 100% full load burn-in test
- Withstand 5G vibration test
- High efficiency , long life and high reliability
- 1 year warranty




MODEL		AK-150-05	AK-150-7.5	AK-150-12	AK-150-13.5	AK-150-15	AK-150-24	AK-150-27	AK-150-48	
Output	DC Voltage Range	5V	7.5V	12V	13.5V	15V	24V	27V	48V	
	Rated Current	20A	20A	12.5A	11.2A	10A	6.3A	5.6A	3.2A	
	Current Range	0 ~ 20A	0 ~ 20A	0 ~ 12.5A	0 ~ 11.2A	0 ~ 10A	0 ~ 6.3A	0 ~ 5.6A	0 ~ 3.2A	
	Rated Power	100W	150W	150W	151.2W	150W	151.2W	151.2W	153.6W	
	Ripple & Noise (max.)	Note.2 100 mVp-p	100 mVp-p	100 mVp-p	100 mVp-p	100 mVp-p	120 mVp-p	120 mVp-p	200 mVp-p	
	Voltage Adj. Range	4.5~5.5V	6.75~8.25V	10.8~13.2V	12.15~14.9V	13.5~16.5V	21.6~26.4V	24.3~29.7V	43.2~52.8V	
	Voltage Tolerance	Note.3 ±2%	±1.5%	±1%	±1%	±1%	±1%	±1%	±1%	
	Line Regulation	±1%	±1%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	
	Load Regulation	±1%	±1%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	
	Setup, Rise Time	<2500ms, <110ms at full load								
Hold up Time (Typ.)	> 32ms / 230VAC, >10ms / 115VAC at full load									
Input	Voltage Range	Note.4 90 ~ 264VAC	127 ~ 370VDC							
	Frequency Range	50 / 60Hz								
	Power Factor (Typ.)	>0.92 / 230VAC		>0.98 / 115VAC at full load						
	Efficiency (Typ.)	79%	82%	86%	87%	87%	87%	89%	89%	
	AC Current (Typ.)	1.8 A / 115VAC		0.9A / 230VAC						
	Inrush Current (Typ.)	30A / 115VAC		55A / 230VAC						
Leakage Current	< 2mA / 230VAC									
Protection	Over Load	> 105% rated output power Protection type : Hiccup mode, recovers automatically after fault condition is removed								
	Over Voltage	115% ~ 150% rated output voltage Protection type : latch-off mode								
	Over Temperature	90°C ±5°C detect on Air Protection type : shut down o/p voltage, after temperature goes down and re-power ON to recover								
Environment	Working Temp.	-20°C ~ +70°C (Refer to output load de-rating curve)								
	Working Humidity	20 ~ 90% R.H non-condensing								
	Storage Temp., Humidity	-40 ~ +85°C 10 ~95% R.H								
	Temp.Coefficient	±0.03%/°C (0 ~ 50°C)								
	Vibration	10 ~ 500Hz, 5G 0.5Oct/min, period for 60 min. Each along X,Y,Z axes								
Safety & EMC Note.5	Safety Standards	UL60950-1, TUV EN60950-1 Approved								
	Green Energy	ENERGY STAR® Single Voltage External AC – DC and AC – AC Power Supplies Eligibility Criteria (Version 1.1)								
	Withstand Voltage	I/P - O/P : 3KVAC, I/P - FG : 1.5KVAC, O/P - FG : 0.5KVDC, 1minute								
	Isolation Resistance	I/P - O/P : 3KVAC(4242 DC) I/P - FG : 1.5KVAC(2121 DC) O/P-FG : 0.5KVAC(707DC), 1 min								
	EMI Conduction & Radiation	EN55022 : 1998+A1 : 2000+A2 : 2003 Class B								
	Harmonic Current	EN61000-3-2 :2000+A2:2005 Class A, EN61000-3-3 : 1995+A1 : 2001								
EMS Immunity	EN61204-3: 2000, EN50204 1998+A1 : 2001+A2 : 2003 light industry level, criteria A									
Others	MTBF	161K HRS Compliance : MIL-HDBK-217F								
	Cooling	Cooling by free convection								
	Dimension (WxHxD)(mm/inch)	197x98x42mm / 7.76x3.86x1.65inch								
	Packing	0.7kg ; 24Pcs/16.8kg								
Note	1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature. 2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. 3. Tolerance: includes set up tolerance, line regulation and load regulation. 4. De-rating may be needed under low input voltages. Please check the de-rating curve for more details. 5. The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives. 6. In parallel connection, maybe only one unit operate if the total output load is less than 5% of rated load condition.									

Specifications subject to change without notice

AK 150


Mechanical Specification

Unit : mm



De-rating Curve

Load VS. Temp.



Load VS. I/P Voltage

Ta=25°C

