

Multiple relay module - UMK- 4 RM 24 - 2971344

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, for 4 plug-in miniature relays or miniature optocouplers, with LED, 24 V AC/DC input voltage

The illustration shows a version for 4 pluggable miniature switching relays or miniature optocouplers



Key commercial data

package_quantity	1
GTIN	4017918088330

Technical data

Note:

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	67.5 mm
Height	77 mm
Depth	59 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Input data

Nominal input voltage U_N	24 V AC/DC $\pm 10\%$
Input voltage range in reference to U_N	0.8 ... 1.1
Typical input current at U_N	2 mA
Type of protection	Bridge rectifier
Protective circuit/component	Bridge rectifier
Status display/channel	Yellow LED

Output data

Contact type	1 PDT
--------------	-------

Multiple relay module - UMK- 4 RM 24 - 2971344

Technical data

Output data

Maximum switching voltage	250 V AC/DC
Limiting continuous current	6 A
Maximum inrush current	8 A
Error detection (line break / short-circuit)	no

General

No. of channels	4
Compatible components	Miniature relays or miniature optocouplers
With components	No
Test voltage	2.5 kV (50 Hz, 1 min.)
Test voltage input/output	2.5 kV AC
Standards/regulations	DIN VDE 0110
Mounting position	Any
Assembly instructions	In rows with zero spacing
Housing insulation material	PVC, side panel PA non-reinforced,
Color	green

Connection data for connection 1

Number of connections	1
Connection method	Screw connection
Number of positions	6
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Screw thread	M3
Stripping length	8 mm

classifications

eCl@ss

eCl@ss 4.0	27371102
eCl@ss 4.1	27371102
eCl@ss 5.0	27371001
eCl@ss 5.1	27371001
eCl@ss 6.0	27371001
eCl@ss 7.0	27371001
eCl@ss 8.0	27371001

ETIM

ETIM 2.0	EC000196
----------	----------

Multiple relay module - UMK- 4 RM 24 - 2971344

classifications

ETIM

ETIM 3.0	EC000196
ETIM 4.0	EC000196
ETIM 5.0	EC000196


UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121543
UNSPSC 11	39121543
UNSPSC 12.01	39121543
UNSPSC 13.2	39121543

approvals

GOST /

Approval details



Drawings

Circuit diagram

