


## CP T SNT 70W 12V 6A

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



The powerful new line of PRO-H power supplies – with ATEX and Class I Div. 2 approvals – is designed for use in Ex zones and the high-performance sector. High power reserves, a wide operating temperature range of -25 °C to +70 °C and high MTBF values (mean time between failures) of up to 1.8 million hours: these features ensure that the power supplies are suitable for all applications that require superior reliability (for example in the processing industry, power engineering, and in demanding machine construction applications). Solutions are available to fit control voltages from 12V/24V to 48V. The product can be wired in parallel in order to increase the power capacity. A two-channel set-up with 100% load sharing can also be implemented with an optional redundancy module. This serves to increase your operational reliability. The Remote On/Off function allow you to switch the device on and off remotely. The output status can be signalled over a voltage-free relay or transistor output. The devices are equipped with pluggable connection terminals which allow them to be easily tested. Product solutions can be custom-fit for use in different types of one-phase, and three-phase systems.

### General ordering data

Type	CP T SNT 70W 12V 6A
Order No.	<a href="#">1105430000</a>
Version	Power supply, switch-mode power supply unit
GTIN (EAN)	4032248880591
Qty.	1 pc(s).

## CP T SNT 70W 12V 6A

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Width	35 mm	Height	110 mm
Depth	110 mm	Weight	0.5 kg
Net weight	519 g		

### Temperatures

Humidity	0...95 % (no condensation)	Operating temperature	-25 °C...+70 °C
Storage temperature	-25 °C...+85 °C		

### Input

AC current consumption	1 A @ 230 V AC, 2 A @ 115 V AC	AC input voltage range	85...264 V AC
Frequency range AC	47...63 Hz	Input fuse (internal)	4 A
Inrush current	< 20 A (230 V AC)	Recommended back-up fuse	6...16 A, char. B, circuit breaker
Wire connection method	Screw connection	rated input voltage	100...240 V AC (wide-range input)

### output

Output voltage type	DC	Output voltage, max.	14 V
Output voltage, min.	12 V	Output voltage, note	(adjustable via potentiometer on front)
Parallel connection option	yes, max. 5	Rated (nominal) output current @ $U_{Nom}$	6 A @ 40 °C
Wire connection method	Screw connection	continous output current @ 24 V DC	6 A @ 40 °C, 5.4 A @ 60 °C, 4.5 A @ 70 °C
rated output voltage	12 V DC $\pm$ 1 %	residual ripple, breaking spikes	100 mV <sub>SS</sub> @ 12 V DC, $I_{nom}$

### General data

AC failure bridging time @ $I_{Nom}$	min. 20 ms @ 230 V AC, min. 10 ms @ 115 V AC	Current limiting	> 100 % $I_N$
Degree of efficiency	typ. 82 % @ 230 V AC	Housing version	Metal, corrosion resistant
Humidity	0...95 % (no condensation)	Indication	Dual LED Operational: green LED, Error: red LED
MTBF	> 1.8 mill. h	Mounting position, installation notice	Horizontal on TS35 rail, with 80 mm of clearance at top and bottom for air circulation; can be aligned side-by-side with 50 mm gap in between.
Operating temperature	-25 °C...+70 °C	Weight	0.5 kg

### EMC / shock / vibration

Limiting of mains voltage harmonic currents	in accordance with EN 61000-3-2	Noise emission acc. to EN55022	Class B
Vibration resistance IEC 60068-2-6	3 axes, sinus, 10...55 Hz, 1 g, 1 oct/min.	Interference immunity test acc. to	EN 61000-4-2 (ESD)  EN 61000-4-3 and EN 61000-4-8 (fields)  EN 61000-4-4 (burst)  EN 61000-4-5 (surge)  EN 61000-4-6 (conducted)  EN 61000-4-11 (dips)
Shock resistance IEC 60068-2-27	3 axes, half sinus, 15 g, 11 ms		

Erstellungs-Datum December 17, 2013 10:15:55 AM CET

## CP T SNT 70W 12V 6A

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Insulation coordination

Class of protection	I, with PE connection	Insulation voltage	4 kV (input / output)
Pollution severity	2		

### Electrical safety (applied standards)

Electrical machine equipment	Acc. to EN60204	For use with electronic equipment	Acc. to EN50178 / VDE0160
Safety extra-low voltage	SELV in accordance with EN60950	Safety transformers for switch-mode power supplies	in accordance with EN 61558-2-4

### Connection data (input)

Conductor cross-section, AWGcmil , max.	12	Conductor cross-section, AWGcmil , min.	24
Conductor cross-section, flexible , min.	0.5 mm <sup>2</sup>	Conductor cross-section, rigid , max.	2.5 mm <sup>2</sup>
Conductor cross-section, rigid , min.	0.5 mm <sup>2</sup>	Number of terminals [Input]	3 for L/N/PE
Tightening torque, max.	0.6 Nm	Tightening torque, min.	0.5 Nm
Wire connection cross section, flexible (input), max.	2.5 mm <sup>2</sup>		

### Connection data (output)

Conductor cross-section, AWGcmil , max.	12	Conductor cross-section, AWGcmil , min.	18
Conductor cross-section, flexible , max.	2.5 mm <sup>2</sup>	Conductor cross-section, flexible , min.	1 mm <sup>2</sup>
Conductor cross-section, rigid , max.	2.5 mm <sup>2</sup>	Conductor cross-section, rigid , min.	1 mm <sup>2</sup>
Number of terminals [Output]	2 (+ / -)	Tightening torque, max.	0.6 Nm
Tightening torque, min.	0.5 Nm		

### Connection data (signal)

Number of terminals [Signal]	3	Wire connection method [Signal]	Pluggable screw connection
Wire cross-section, AWGcmil [Signal], max.	12	Wire cross-section, AWGcmil [Signal], min.	32
Wire cross-section, solid [Signal], max.	2.5 mm <sup>2</sup>	Wire cross-section, solid [Signal], min.	0.2 mm <sup>2</sup>

### Signalling

Active output signal	11 V DC ± 1 V DC / max. 20 mA	Power Good Signal	Trigger point 9...11 V DC
----------------------	----------------------------------	-------------------	---------------------------

**CP T SNT 70W 12V 6A**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**Approvals**

Institute (CSA)		Certificate No. (CSA)	246286-2148800
Institute (UL)		Certificate No. (UL)	E236157
Institute (cULus)		Certificate no. (cULus)	E258476CON_1
Institute (cURus)		Certificate No. (cURus)	E255651CONV

**Rated data UL**

Certificate No. (UL)	E236157
----------------------	---------

**Classifications**

eClass 6.2	27-04-90-04	eClass 7.1	27-04-90-04
------------	-------------	------------	-------------

**Product information**

Descriptive text ordering data	The internal varistor found in a switch-mode power unit does not replace the necessary surge protection in a system.
--------------------------------	----------------------------------------------------------------------------------------------------------------------

**Approvals**

Approvals	
ROHS	Conform

**Downloads**

Package insert	<a href="#">Operating Instructions</a>
Declaration of Conformity	<a href="#">K491_05_12.pdf</a>
PDF	<a href="#">Warrenty Information</a>