

Sensor/actuator box - PSR-SACB-4/4-L-10,0PUR-SD - 2981884

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



The sensor box PSR-SACB for safety limit switches safely interconnects up to 4 connected limit switches, each with 1 N/C contact and 1 N/O contact, to a safety relay combination, e.g. PSR-SDC4, cable length: 10 m

Product Features

- Safety in the field, thanks to robust housing and high degree of protection
- Flexible, distributed bundling of signals in one master cable
- Convenient: increased machine availability thanks to quick and easy diagnostics

Key commercial data

package_quantity	1
GTIN	4046356167987

Technical data

Dimensions

Width	54 mm
Height	82 mm
Depth	19 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Degree of protection	IP65/67
Ambient temperature (operation)	-30 °C ... 70 °C (for fixed installation)
Ambient temperature (operation)	-5 °C ... 70 °C (for flexible installation)

Master cable

Cable type	Master cable suitable for flexible cable conduit
Fixed cable length	10 m
Signal line cross section, stranded	6x 0.34 mm ²
Power supply cross section, stranded	2x 0.75 mm ²
External diameter	8.2 mm

General

Number of positions	4
Number of slots	4
Status display	Yellow LED

Sensor/actuator box - PSR-SACB-4/4-L-10,0PUR-SD - 2981884

Technical data

General

Max. permissible current	100 mA (per signal output)
Max. permissible total current	100 mA (alarm outputs)
Nominal operating mode	100% operating factor
Mounting position	Any
Assembly instructions	In rows with zero spacing
Name	Air and creepage distances
Standards/regulations	DIN EN 50178
Rated surge voltage / insulation	0.8 kV
Rated insulation voltage	50 V DC
Pollution degree	2
Surge voltage category	III
Insulating material (housing)	PA 6.6
Inflammability class according to UL 94	V0

classifications

eCl@ss

eCl@ss 4.0	27371102
eCl@ss 4.1	27371102
eCl@ss 5.0	27371901
eCl@ss 5.1	27371901
eCl@ss 6.0	27371819
eCl@ss 7.0	27371819
eCl@ss 8.0	27371819

ETIM

ETIM 2.0	EC000196
ETIM 3.0	EC001449
ETIM 4.0	EC000196
ETIM 5.0	EC002585

UNSPSC

UNSPSC 6.01	30211901
UNSPSC 7.0901	39121501
UNSPSC 11	39121501
UNSPSC 12.01	39121501
UNSPSC 13.2	39121501


approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized /

Sensor/actuator box - PSR-SACB-4/4-L-10,0PUR-SD - 2981884

approvals

Approval details



accessories

Short-circuit connector

SAC-2P-M12MS ASI TR - 1539570



Device marking


ZBN 18:UNBEDRUCKT - 2809128



Drawings


Sensor/actuator box - PSR-SACB-4/4-L-10,0PUR-SD - 2981884

Connection diagram



Sensor/actuator box - PSR-SACB-4/4-L-10,0PUR-SD - 2981884

Block diagram



Sensor/actuator box - PSR-SACB-4/4-L-10,0PUR-SD - 2981884

Dimensioned drawing

