

# Solid-state relay terminal block - DEK-OV- 5DC/ 24DC/ 3 - 2941361

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Power solid-state relay terminal block, input: 5 V DC, output: 3 - 30 V DC/3 A, terminal block width: 6.2 mm

The illustration shows the version DEK-OV- 24DC/24DC/3

## Product Features

- EB-DIK insertion bridges
- Actuator version available
- Labeling and mounting with user-friendly modular terminal blocks
- Wear-free switching of up to 24 V DC/10 A or 240 V AC/800 mA
- Integrated output protective circuit
- Status indicator
- Integrated input circuit
- Zero voltage switch at AC output
- Electrical isolation between input and output at up to 2.5 kVrms



## Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4017918080389

## Technical data

Note:

<b>Utilization restriction</b>	EMC: class A product, see manufacturer's declaration in the download area
--------------------------------	---

### Dimensions

<b>Width</b>	6.2 mm
<b>Height</b>	80 mm
<b>Depth</b>	56 mm

### Ambient conditions

<b>Ambient temperature (operation)</b>	-20 °C ... 60 °C
<b>Ambient temperature (storage/transport)</b>	-20 °C ... 70 °C

### Input data

# Solid-state relay terminal block - DEK-OV- 5DC/ 24DC/ 3 - 2941361

## Technical data

### Input data

Nominal input voltage $U_N$	5 V DC
Input voltage range in reference to $U_N$	0.8 ... 1.2
Switching threshold "0" signal in reference to $U_N$	$\leq 0.4$
Switching threshold "1" signal in reference to $U_N$	$\geq 0.8$
Typical input current at $U_N$	11 mA
Typical response time	40 $\mu$ s
Typical turn-off time	200 $\mu$ s
Operating voltage display	Yellow LED
Type of protection	Protection against polarity reversal
Transmission frequency	300 Hz

### Output data

Output voltage range	3 V DC ... 30 V DC
Limiting continuous current	3 A (see derating curve)
Voltage drop at max. limiting continuous current	$\leq 0.2$ V
Output circuit	2-wire, floating
Type of protection	Protection against polarity reversal
Type of protection	Surge protection
Protective circuit/component	Polarity protection diode

### Connection data

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	2.5 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	14

### General

Test voltage input/output	2.5 kV AC
Test voltage input/output	2.5 kV (50 Hz, 1 min.)
Mounting position	Any
Assembly instructions	In rows with zero spacing
Operating mode	100% operating factor
Name	Standards/regulations
Standards/regulations	IEC 60664
Standards/regulations	EN 50178
Standards/regulations	IEC 62103
Rated surge voltage / insulation	Basic insulation
Pollution degree	2

# Solid-state relay terminal block - DEK-OV- 5DC/ 24DC/ 3 - 2941361

## Technical data

### General

Surge voltage category	III
------------------------	-----

### classifications

#### eCl@ss

eCl@ss 4.0	27371102
eCl@ss 4.1	27371102
eCl@ss 5.0	27371001
eCl@ss 5.1	27371001
eCl@ss 6.0	27371001
eCl@ss 7.0	27371001
eCl@ss 8.0	27371001

#### ETIM

ETIM 2.0	EC001504
ETIM 3.0	EC001504
ETIM 4.0	EC001504
ETIM 5.0	EC001504

#### UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121542
UNSPSC 11	39121542
UNSPSC 12.01	39121542
UNSPSC 13.2	39121542

### approvals

GOST /

#### Approval details



### accessories

#### Bridge

## Solid-state relay terminal block - DEK-OV- 5DC/ 24DC/ 3 - 2941361 accessories

EB 80- DIK WH - 2715788



EB 80- DIK RD - 2715953



EB 80- DIK BU - 2715940



EB 10- DIK BU - 2716680



EB 5- DIK BU - 2716677



EB 4- DIK BU - 2716664



## Solid-state relay terminal block - DEK-OV- 5DC/ 24DC/ 3 - 2941361 accessories

---

EB 3- DIK BU - 2716651



EB 2- DIK BU - 2716648



EB 10- DIK RD - 2716774



EB 5- DIK RD - 2716761



EB 4- DIK RD - 2716758



# Solid-state relay terminal block - DEK-OV- 5DC/ 24DC/ 3 - 2941361

accessories

EB 3- DIK RD - 2716745




EB 2- DIK RD - 2716693



## Drawings

Diagram



- 1 Horizontal mounting
- 2 Vertical mounting

# Solid-state relay terminal block - DEK-OV- 5DC/ 24DC/ 3 - 2941361

Circuit diagram

