

# Relay connectors - ST-REL3-KG230/21 - 2822406

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Relay connector, fitted with miniature switching relay, contacts (AgNi): Medium to large loads, 1 PDT, 230 V AC input voltage, with light indicator, can be plugged into basic terminal blocks

The illustration shows version ST-REL3-KG 24/21

## Key commercial data

package_quantity	10
GTIN	4017918077266

## Technical data

### Dimensions

Width	20.8 mm
Height	33 mm
Depth	66.5 mm

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

### Coil side

Nominal input voltage $U_N$	230 V AC/DC
Input voltage range in reference to $U_N$	0.8 ... 1.06
Nominal input current at $U_{IN}$	5 mA
Typical response time	6 ms
Typical release time	7 ms (with DC)
Operating voltage display	Yes
Protective circuit	Bridge rectifier, varistor

### Contact side

Contact type	Single contact, 1-PDT
Contact material	AgNi
Maximum switching voltage	250 V AC/DC
Maximum inrush current	8 A
Limiting continuous current	6 A
Interrupting rating (ohmic load) max.	95 W (at 24 V DC)
Interrupting rating (ohmic load) max.	50 W (at 48 V DC)

# Relay connectors - ST-REL3-KG230/21 - 2822406

## Technical data

### Contact side

Interrupting rating (ohmic load) max.	45 W (at 60 V DC)
Interrupting rating (ohmic load) max.	35 W (at 110 V DC)
Interrupting rating (ohmic load) max.	55 W (at 220 V DC)
Interrupting rating (ohmic load) max.	1500 VA (for 250 V AC)

### General

Test voltage relay winding/relay contact	2.5 kV AC (50 Hz, 1 min.)
Operating mode	100% operating factor
Mechanical service life	Approx. $2 \times 10^7$ cycles
Standards/regulations	DIN VDE 0110b, Gr. C for 250 V DC
Standards/regulations	IEC 60255/DIN VDE 0435 (in relevant parts)
Standards/regulations	DIN EN 50178/DIN VDE 0160 (in relevant parts)
Standards/regulations	EN 60730/DIN VDE 0631
Standards/regulations	DIN VDE 0160 (in relevant parts)

## classifications

### eCl@ss

eCl@ss 4.0	27371104
eCl@ss 4.1	27371104
eCl@ss 5.0	27371001
eCl@ss 5.1	27371001
eCl@ss 6.0	27371001
eCl@ss 7.0	27371001
eCl@ss 8.0	27371001

### ETIM

ETIM 2.0	EC000196
ETIM 3.0	EC000196
ETIM 4.0	EC000196
ETIM 5.0	EC000196

### UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121515
UNSPSC 11	39121515
UNSPSC 12.01	39121515
UNSPSC 13.2	39121515


## approvals

GOST / GOST /

# Relay connectors - ST-REL3-KG230/21 - 2822406


approvals

Approval details



Drawings

Circuit diagram





© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>