

Power storage devices - MINI-BAT/24DC/0.8AH - 2866666

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Power storage device, lead AGM, VRLA technology, 24 V DC, 0.8 Ah.



Key commercial data

package_quantity	1
GTIN	4046356152129

Technical data

Dimensions

Width	67.5 mm
Height	99 mm
Depth	107 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	0 °C ... 40 °C
Max. permissible relative humidity (operation)	95 %

Input data

Nominal input voltage	24 V DC
Buffer period	20 min (1 A)
Buffer period	7 min (2 A)

Output data

Nominal output voltage	24 V DC
Output current	max. 5 A
Connection in parallel	5
Connection in series	No
Output fuse	5 A

General

IQ technology	No
---------------	----

Power storage devices - MINI-BAT/24DC/0.8AH - 2866666

Technical data

General

Disposal	Used batteries must not be thrown away with household waste, they should instead be disposed of in accordance with applicable national regulations. They can also be returned to Phoenix Contact or the manufacturer.
Net weight	0.9 kg
Protection class	III
UL approvals	UL ANSI/ISA-12.12.01 Class I, Division 2, Groups A, B, C, D (Hazardous Location)

classifications

eCl@ss

eCl@ss 4.0	27040603
eCl@ss 4.1	27040603
eCl@ss 5.0	27040603
eCl@ss 5.1	27040603
eCl@ss 6.0	27040603
eCl@ss 7.0	27040603
eCl@ss 8.0	27040603

ETIM

ETIM 2.0	EC000382
ETIM 3.0	EC000382
ETIM 4.0	EC000382
ETIM 5.0	EC000357

UNSPSC

UNSPSC 6.01	30211510
UNSPSC 7.0901	39121011
UNSPSC 11	39121011
UNSPSC 12.01	39121011
UNSPSC 13.2	39121011

approvals

UL Listed / cUL Listed / cULus Listed /

Approval details



Power storage devices - MINI-BAT/24DC/0.8AH - 2866666

approvals



Drawings

Block diagram

