



DATA SHEET	53019000
SKINTOP® GMP-GL	valid from : 22.12.2011

The SKINTOP® GMP-GL, a hexagonal locknut of polyamide, glass fiber reinforced, is used where cable glands are attached but there is only a passthrough whole.
When the cable gland is fixed in a thread, a higher protection against vibration can be attained with this locknut.



Technical features:

Material: polyamide, glass fiber reinforced UL94 V2
Sizes: PG 7 - PG 48 in acc. to DIN 46320
Temperature range: - 20° C up to + 80° C
Colour: RAL 9005, RAL 7001 and RAL 7035

Approval:



Note:

SKINTOP® GMP-GL UL- approved only by use with the UL – approved SKINTOP® polyamide cable glands.

For more information please see our current catalogue.
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: R. Drotleff	Document: DB53019000_3EN	page 1 of 1
--------------------------------------	--------------------------	-------------