

Autotransformer **JET 250**



Advantages

Integrated short circuit and overload protection

Very high efficiency

Very good moisture protection and low noise thanks to XtraDenseFill resin encapsulation

Carrying handle, mains connecting lead NEMA5-15 (USA) and socket for mobile use

Applications

Autotransformer for mobile use for the adjustment of the voltage in 110 Vac networks to 230 Vac equipment when no electrical isolation is required.

Standards

Autotransformer
to: VDE 0570 Part 2-13, DIN EN 61558-2-13, EN 61558-2-13,
IEC 61558-2-13

Approvals



Autotransformer JET 250

Type		JET 250
Electrical data	Input	
	Rated input voltage	110 Vac
	Rated frequency	50 - 60 Hz
	Output	
	Rated output voltage	230 Vac
	Rated Power	250 VA
	No-load voltage (app. x factor)	1.04
	Efficiency	94 %
	Environment	
	Ambient temperature max.	40 °C
	Safety and protection	
	Type	Resin encapsulated transformer
	Class of Insulation System	A
	Protection index	IP 22
	Safety class	I
Short circuit strength	non-inherently short-circuit proof	
Order numbers		
Order Number	JET 250	

Type		JET 250
Mechanical data	Input	
	Terminals Input	Connecting cable with NEMAS-15 plug (USA)
	Output	
	Terminals Output	Protective contact socket
Measures and weights		
Weight	3.10 kg	

Subjects to change.