

# PRODUCT DATASHEET

## DERAY - IB

**coloured**

Heat shrinkable sleeve – radiation cross-linked

Technical Data		Current Values	Test Methods
	<b>Material</b>  <b>Surface</b> <b>Specific Gravity</b> <b>Longitudinal Shrinkage</b> <b>Shrink Ratio</b>	PE, modified, lead and cadmium free matt 1.10 g/cm <sup>3</sup> max. -10% max. 2:1	ASTM-D 792, A-I ASTM-D 2671
<b>Mechanical Properties</b>	<b>Tensile Strength</b> <b>Elongation</b> <b>Secant Modulus</b>	16 MPa 450 % 125 MPa max.	IEC 60684-2 IEC 60684-2 ASTM-D 882
<b>Thermal Properties</b>	<b>Thermal Aging</b> <b>Tensile Strength</b> <b>Elongation</b>  <b>Thermal Shock</b> <b>Tensile Strength</b> <b>Elongation</b>  <b>Cold Bend Test</b> <b>flammability</b> <b>Shrink Temperature</b> <b>Storage Temperature</b> <b>Continuous Operating Temperature</b>	(168 hrs at 158 °C) 12 MPa 350 %  (4 hrs at 200 °C) 13 MPa 300 %  does not break at -55°C passed +100°C to +200°C +40°C max. -55°C to +120°C	UL 224    IEC 811-1-2   ASTM-D 2671 Meth. C MVSS 302   IEC 216
<b>Chemical Properties</b>	<b>Corrosive Action</b> <b>Compatibility with Copper</b> <b>Resistance against Chemicals</b> <b>Water Absorption</b>	Non-corrosive Non-corrosive Good 0.20% max	ASTM-D 2671 Meth. A ASTM-D 2671 Meth. B   VDE 0473
<b>Electrical Properties</b>	<b>Dielectric Strength</b> <b>Specific Volume Resistance</b>	22 kV/mm 10 <sup>15</sup> Ω x cm	VDE 0303 Part 2 VDE 0303 Part 3
<b>Printability</b>	<b>Hot stamp printing</b> <b>Ink jet printing</b> <b>Offset printing</b>	Very good Very good good	

Subject to modification.

All Information contained in this preliminary datasheet is believed to be reliable. We advise however that customers should separately evaluate the suitability of our products for their particular application. DSG-Canusa GmbH gives no guarantees in respect of the accuracy or sufficiency of the information presented and disclaim any liability regarding its use. Our responsibilities are only those listed in our Standard Terms and Conditions of Sale for these products. In no instance will we be liable for any eventual, indirect, or consequential damage or damages arising from the sale, resale, transfer, use or misuse of the product.