

# Elma TT

## Logistik GmbH

Constructional data for isolating transformers and safety transformers:

- 1.3 Reference of type : PV/1-21456  
1.4 Trade mark : CONRAD  
1.5 Other markings : IZ 64 - Conrad Art. Nr. 514314  
1.6 Europe standard : EN 61558 - 2 - 6

- 2.1 Protection against electric shock : Non short.circuit proof  
2.2 Class of protection to IEC 529 : IP 00  
2.3 Type of construction (Isolating transformer, Transformer for toys) : Safety-isolating transformer  
2.4 Stationary Transformer : Stationary, to built-in transformer  
Portable Transformer :  
2.5 Protection against short-circuit according to Sub-clause  
inherently short-circuit proof :  
non-inherently short-circuit proof :  
non short-circuit proof : Non short-circuit proof  
fail safe  
(rated current of the cutout)  
2.6 Rated maximum ambient temperature :  $t_a$  40 °C  
2.7 Class : B Insulation : IEC 60 085 and IEC 60 216

### 3. Electrical values

		prim :	sec:
3.1 Rated voltage(s)	V :	230	12 – 14 – 16 – 18 – 24
3.2 Rated frequency	Hz :	50	
3.3 Rated current	A :	0,23	2,2
3.4 Rated output	VA :		52,8

### 4. Windings

- 4.1 Coil base, number : 1  
material : Duretan AKV 30 H – PA 6.6  
4.2 Material of layer insulation : Film poliestere 0.13 , classe B-130 - Teflex  
4.3 Windings, number : 1090 62 + 12 + 12 + 13 + 34  
material : Enoflex G1 – S180 Enoflex G1 – S180


4.4 Diameter of wire (mm) : 0,315 0,9  
 4.5 Windings insulation, material : polyurethane polyamide polyurethane polyamide

## 5. Iron core

5.1 Sheet metall, material : EI 84 V 530 – 50  
 main dimensions : 84x70x28  
 5.2 Cross-sectional drawing : See specification of insulation materials

## 6. Type of construction

6.1 Open – Covered – In case protection : Open  
 6.2 Impregnated – Undrowned – Drowned : Impregnated  
 6.3 Soaking (liquor) :  
 6.4 Underpressure – Overpressure – Soaking at : Soaking  
 6.5 Drown material : 1K – Deatech Nr. 822.125



A(mm)	B(mm)	C(mm)	D(mm)	E(mm)	F(mm)	Weight (kg)
88	70	58	56	45	84	1,4

## 7. Label

**514 314**

**52.8VA / 2.2A**



---

**1 - 3= 230V**

---

**15= 0V**

**8= 16V**

**9= 12V**

**6= 18V**

**11= 14V**

**13= 24V**

ELMA TT

13.01.2010