

Elma TT

Logistik GmbH

Constructional data for isolating transformers and safety transformers:

1.3 Reference of type : PV/1-21692
1.4 Trade mark : CONRAD
1.5 Other markings : IZ 69 - Conrad Art. Nr. 514349
1.6 Europe standard : EN 61558 - 2 - 6

2.1 Protection against electric shock : Non short.circuit proof
2.2 Class of protection to IEC 529 : IP 00
2.3 Type of construction (Isolating transformer, Transformer for toys) : Safety-isolating transformer
2.4 Stationary Transformer : Stationary, to built-in transformer
Portable Transformer :
2.5 Protection against short-circuit according to Sub-clause
inherently short-circuit proof :
non-inherently short-circuit proof :
non short-circuit proof : Non short-circuit proof
fail safe
(rated current of the cutout)
2.6 Rated maximum ambient temperature : t_a 40 °C
2.7 Class : B Insulation : IEC 60 085 and IEC 60 216

3. Electrical values

		prim :	sec:
3.1 Rated voltage(s)	V :	230	4-6-8-10-12-14-16-18-20-24
3.2 Rated frequency	Hz :	50	
3.3 Rated current	A :	0,42	4,0
3.4 Rated output	VA :		96

4. Windings

4.1 Coil base, number : 1
material : Duretan AKV 30 H – PA 6.6
4.2 Material of layer insulation : Film poliestere 0.13 , classe B-130 - Teflex
4.3 Windings, number : 727 20+34+7+7+14
material : Enoflex G1 – S180 G2 Mediotherm 200
4.4 Diameter of wire (mm) : 0,4 1,2

4.5 Windings insulation, material : polyurethane polyamide polyamide-imide

5. Iron core

5.1 Sheet metall, material : EI 84 V 530 – 50

main dimensions : 84x70x43

5.2 Cross-sectional drawing : See specification of insulation materials

6. Type of construction


6.1 Open – Covered – In case protection : Open

6.2 Impregnated – Undrowned – Drowned : Impregnated

6.3 Soaking (liquor) :

6.4 Underpressure – Overpressure – Soaking at : Soaking

6.5 Drown material : 1K – Deatech Nr. 822.125



A(mm)	B(mm)	C(mm)	D(mm)	E(mm)	F(mm)	Weight (kg)
88	70	73	56	60	84	2,0

7. Label

514 349



96VA / 4A

1 - 7 = 230V

20-17 = 4V 4-14 = 12V

11- 4 = 6V 4-17 = 14V 11-17 = 20V

10-20 = 8V 11-10 = 16V 11-20 = 24V

4-10 = 10V 4-20 = 18V

ELMA TT

13.01.2010