


Product Description

Reliable bending and anti-kink protection; Cable conservation; Functional reliability; To protect flexible cables



Application range

- Cables for electrical appliances and machinery that are moved under normal use must be protected against excessive bending as required in accordance with VDE 0730.
- Handheld device
- Robotics industry
- Light and sound applications
- Moving machine parts

Benefits

- Reliable bending and anti-kink protection
- Cable conservation
- Functional reliability
- To protect flexible cables

Design

- PG connection thread



Approvals

- UL File Nr. E79903

Note

- Refer to SKINTOP® PG accessories for suitable accessories
- Counter nut to be used: SKINTOP® GMP-GL
- Version with smaller insert to seal smaller cable cross-sections, SKINTOP® BSR, is available upon request

Technical Data

Caution

Refer to Appendix T21 for the installation dimensions and torques

Colour delivered

Silver grey (RAL 7001) Black (RAL 9005),

UV-resistant

Material

Body: Polyamide Seal: CR

Protection rating

IP 68 - 5 bar

Temperature range

-20°C to +80°C

Article List

Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Overall length/ C (mm)	Thread length/ D (mm)	Pieces / PU
SKINTOP® BS silver grey						
53015600	BS 7	2,5 - 6,5	15	62.0	8.0	100
53015610	BS 9	3,5 - 8	19	73,5	8.0	100
53015620	BS 11	4 - 10	22	86.0	8.0	100
53015630	BS 13,5	6 - 12	24	98.0	9.0	50
53015640	BS 16	9 - 14	27	111,5	10.0	25
53015650	BS 21	13 - 18	33	129.0	11.0	25
SKINTOP® BS black						
53015800	BS 7	2,5 - 6,5	15	62.0	8.0	100
53015810	BS 9	3,5 - 8	19	73,5	8.0	100
53015820	BS 11	4 - 10	22	86.0	8.0	100



53015830	BS 13,5	6 - 12	24	98.0	9.0	50
53015840	BS 16	9 - 14	27	111,5	10.0	25
53015850	BS 21	13 - 18	33	129.0	11.0	25

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.