



<b>DATA SHEET</b>	52103300
<b>SKINDICHT® SM-PE-M</b>	valid from : 21.10.2009

The SKINDICHT® SM-PE-M is an earth - equipotential locknut, nickel-plated brass with metric thread in accordance to EN 60423  
The SKINDICHT SM-PE is required wherever varnished, anodized and powder coated housings are used. When the locknut is tightened, it cuts through the insulating layer guaranteeing optimum contact.



**Technical features:**

Threads: M12x1.5 up to M110x2 in acc. to EN 60423

Material: nickel- plated brass

Part number	Type size M	Wrench size mm	Thickness mm	Outer Ø
5210 3300	SKINDICHT SM-PE-M 12x1,5	15	4,7	17,32
5210 3310	SKINDICHT SM-PE-M 16x1,5	19	4,7	21,94
5210 3320	SKINDICHT SM-PE-M 20x1,5	24	4,7	27,70
5210 3330	SKINDICHT SM-PE-M 25x1,5	30	5,2	34,60
5210 3340	SKINDICHT SM-PE-M 32x1,5	36	5,7	41,5
5210 3350	SKINDICHT SM-PE-M 40x1,5	46	6,5	53,1
5210 3360	SKINDICHT SM-PE-M 50x1,5	60	6,5	69,28
5210 3370	SKINDICHT SM-PE-M 63x1,5	70	7,0	80,83
5210 3371	SKINDICHT SM-PE-M 75x1,5	85	8,0	95
5210 3372	SKINDICHT SM-PE-M 90x2	102	10	114
5210 3373	SKINDICHT SM-PE-M 110x2	124	12	135

For more information please see our current catalogue.

Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: M. Steinberg	Document: DB52103300_1EN	page 1 of 1
---------------------------------------	--------------------------	-------------