


Product Description

Protects against liquids;High-tensile;High crush-resistance;Suitable for outdoor use and direct burial;High mechanical resistance



Application range

- Mechanical engineering
- Plant engineering
- Outdoors
- Used in areas where liquids are present
- Applications with high mechanical stress

Benefits

- Protects against liquids
- High-tensile
- High crush-resistance
- Suitable for outdoor use and direct burial
- High mechanical resistance

Design

- Spirally-wound metal protective conduit with roughened profile
- PVC outer sheath

**Technical Data****Colour delivered**

Black (RAL 9005)

Temperature range

-20°C to +70°C Short-term: up to +100°C

Article List

Part number	Article designation	Internal Ø x external Ø (mm)	Bending radius (mm)	Inner Ø (mm)	Suitable for SILVYN® LGF-2-M/LGS-2-M	Suitable for SILVYN® LGS-2	PU ring (m)
SILVYN® LCC-2							
61804702	LCC-2/10	6,8 x 10	25	6.8	M 12 x 1,5	7	30
61804712	LCC-2/12	10,2 x 14	30	10.2	M 16/1 x 1,5	9	30
61804722	LCC-2/16	13 x 17	40	13	M16/2 + 20/1x1,5	11	30
61804732	LCC-2/20	16,9 x 21,5	45	16.9	M 20/2 x 1,5	13,5 + 16	30
61804742	LCC-2/25	21,1 x 26	55	21.1	M 25 x 1,5	21	30
61804752	LCC-2/32	28,1 x 34	70	28.1	M 32 x 1,5	29	30
61804762	LCC-2/40	37,6 x 44,5	80	37.6	M 40 x 1,5	36	10
61804772	LCC-2/50	48,4 x 55	90	48.4	M 50 x 1,5		10
61804792	LCC-2/63	57,5 x 64,5	115	57.5	M 63 x 1,5	48	10

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.