



<b>DATA SHEET</b>	53119200
<b>SKINTOP® GMP-HF-M</b>	valid from : 26.04.2007

The SKINTOP® GMP-HF-M, a hexagonal locknut of special polyamide, halogen free, is used where cable glands are attached but there is only a pass-through whole.

When the cable gland is fixed in a thread, a higher protection against vibration can be attained with this locknut.



**Technical features:**

Material:	special polyamide, halogen free V0 (in acc.to UL 94)
Sizes:	M 12x1.5 - M 63x1.5 in acc. to EN 60 423
Temperature range:	- 20°C up to + 100°C
Colour:	RAL 7035

**Note:**

Designed for use in connection with SKINTOP® GMP-HF-M

For more information please see our current catalogue.

Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: M. Steinberg	Document: DB53119200EN	page 1 of 1
---------------------------------------	------------------------	-------------