


Radial Dipped Ceramic Capacitors [General Used Capacitor – 6.3V-1KV]

RDC Series



♦ Features

- □ Advanced process technology produces thinner layers of ceramic dielectric and offers higher voltage rating and capacitance values
- ☐ Provides good frequency response
- ☐ High reliability
- ☐ RoHS compliant
- ☐ Halogen free available

Applications

- ☐ Suitable for Automotive Electronics, Power supplies
- ☐ Inverter and Converter
- ☐ Fuel pump , Water pump , Hybrid engine , Door lock , Wiper

♦ Summary of Specification

Operation Temperature	NPO,X7R : -55~+125 ℃ ; X5R : -55~+85 ℃ ; Y5V : -30~+85 ℃
Rated Voltage	6.3Vdc to 1KVdc
Temperature Coefficient	NPO : ≤ ± 30ppm/ °C , -55~+125 °C (EIA Class I)
	X7R : ≤ ± 15% , -55~+125 °C (EIA Class Ⅱ)
	X5R : ≤ ± 15% , -55~+85 °C (EIA Class Ⅱ)
	Y5V : ≤ +22~ -82% , -30~+85 °C (EIA Class Ⅱ)
Capacitance Range	NPO : 2pF to 220nF
	X7R: 150pF to 22uF
	X5R : 0.1uF to 100uF
	Y5V : 0.1uF to 100uF
Dissipation Factor	Please see RDC specification data sheet
Insulation Resistance	10G Ω or 500/C Ω whichever is smaller
Aging	NPO:0%; X7R,X5R: 2.5 % Y5V: 6% per decade of time
Dielectric Strength	V ≤ 50 : 250% Rated Voltage
	V < 500V :200% Rated Voltage
	500V ≤ V < 1000V: 150% Rated Voltage
	1000 ≤ V :120% Rated Voltage


♦ How To Order


RDC	X	473	K	631	EK	Α	N
Product Code RDC: Radial Ceramic Chip Capacitor	Dielectric Ex.: N: NPO X: X7R B: X5R Y: Y5V	Capacitance Unit: pF Ex.: 2R0:2.0pF 100:10×10° 471:47×10¹ 102:10×10²	Ex.: C:+/-0.25pF D:+/-0.50pF J:+/- 5% K:+/-10% M:+/-20% Z:+80/-20%	Rated Voltage Ex.: 007:6.3Vdc 010:10Vdc 025:25Vdc 050:50Vdc 101:100Vdc 251:250Vdc 631:630Vdc 102:1000Vdc	Leader Style & Dimension Ex: D Type CD:4.5x5.5mm DD:4.5x5.5mm ED:5.5x7.0mm FD:7.5x8.0mm GD:7.6x9.4mm K Type CK:4.5x5.5mm DK:4.5x5.5mm EK:5.5x7.0mm FK:7.5x8.0mm	Lead Length & Packaging Ex.: S:5.0mm M:10.0mm L:25mm min. A: Ammo Box	Optional Suffix Ex.: N :Halogen Free Indicator






♦ Structure & Dimension







					Unit:	mm [inches]
TYPE	L (max)	W (max)	T (max)	F	Ł	Φd
C□	4.5	5.5	2.5	5.0±1	25.0+3/-1	0.5±0.1
	[0.157]	[0.216]	[0.098]	[0.196]	[0.984]	[0.196]
D□	4.5	5.5	2.5	5.0±1	25.0+3/-1	0.5±0.1
	[0.157]	[0.216]	[0.098]	[0.196]	[0.984]	[0.196]
E□	5.5	7.0	4.0	5.0±1	25.0+3/-1	0.5±0.1
	[0.216]	[0.275]	[0.157]	[0.196]	[0.984]	[0.196]
F□	7.5	8.0	4.0	5.0±1	25.0+3/-1	0.5±0.1
	[0.294]	[0.314]	[0.157]	[0.196]	[0.984]	[0.196]
GD	7.6 [0.299]	9.4 [0.370]	6.9 [0.272]		25.0+3/-1 [0.984]	0.6±0.1 [0.196]

♦ Capacitance Range

NPO(N) Series

Туре		C			D[Ę						F			GD
WVDC																		630V	
Cap Min.	5R0	5R0	2R0	100	101	101	100	153	392	332	101	101	100	104	473	223	822	822	101
Cap Max.	332	471	151	103	472	272	681	104	333	153	682	682	102	224	104	473	223	223	183

X7R(X) Series

Туре		C					D							Е				
WVDC	16V	25V	50V	100V	16V	25V	50V	100V	250V	500V	16V	25V	50V	100V	250V	500V	630V	1KV
Cap Min.																		
Cap Max.	474	224	104	183	225	155	334	103	223	223	156	475	155	474	224	683	683	103
Туре				F					GD									
WVDC	16V	25V	50V	100V														
Cap Min.	226	475	104	104	104	683	683	103	474	474	105	224	224	393				
Cap Max.	226	156	475	225	105	224	104	683	106	475	225	474	474	224	1			

X5R(B) Series

710:1(2)														
Type		C				D				Ę			F	
	6.3V													
Cap Min.														
Cap Max.	106	475	225	105	106	475	475	475	226	156	106	106	107	476

Y5V(Y) Series

Type		С					D					E				F[
																		50V
Cap Min.																		
Cap Max.	475	475	225	105	226	106	475	225	105	107	476	226	106	475	107	476	226	106

■ Other dimensions, capacitance values and voltages rating are available. Please contact HEC.





Item	Specification	Test Condition
Operation Temperature	Please see HEC specification data sheet for details	
Visual	No abnormal exterior appearance	Visual Inspection
Capacitance	Within The Specified Tolerance	Class Frequency Voltage
Quality Factor	Class I (NPO): More Than 30pF : Q \geq 1000 30pF & Below: Q \geq 400 + 20C (C:Cap., pF)	NPO C≤100pF 1MHz±10% 1.0±0.2Vrms C>100pF 1KHz±10% X7R/X5R/Y5V
Dissipation Factor	Class II (X7R,X5R,Y5V): Please see HEC specification data sheet for details	$\begin{array}{c cccc} C \leq 10 uF & 1 \text{KHz} \pm 10\% & 1.0 \pm 0.2 \text{Vrms} \\ \hline C > 10 uF & 120 \text{Hz} \pm 20\% & 0.5 \pm 0.2 \text{Vrms} \\ \hline \text{Perform a heat treatment at } 150 \pm 5^{\circ}\text{C} \text{ for 30min.} \\ \text{then place room temp. for } 24 \pm 2 \text{hr.} \end{array}$
Insulation Resistance	10,000M Ω or 500/C Ω whichever is smaller for rated voltage>10V and greater 100/C Ω for rated voltage≤10V	Applied Voltage: Rated Voltage Charge Time: 60±5 sec. Charge-Discharge current shall be less than 50mA current
Withstanding Voltage	No dielectric breakdown or mechanical breakdown	V \leq 50 : 250% Rated Voltage V $<$ 500V : 200% Rated Voltage 500V \leq V $<$ 1000V: 150% Rated Voltage 1000 \leq V :120% Rated Voltage for 1~5 sec. Current is limited to less than 50mA
Temperature Capacitance Coefficient	Char. Temp. Range Cap. Change NPO (N) -55°C ~ +125°C ± 30ppm/°C X7R (X) -55°C ~ +125°C ± 15% X5R (B) -55°C ~ +85°C ± 15% Y5V (Y) -30°C ~ +85°C +22% ~ -82%	Class I: [C2-C1/C1(T2-T1)] × 100% Class II: (C2-C1)/C1 × 100% T1:Standard Temperature(25℃) T2:Test Temperature C1:Capacitance at Standard Temperature C2:Capacitance a Test Temperature
Lead Strength	Tensile Strength No mechanical damage such as lead breakage and loosing. Bending No mechanical damage such as lead Strength . breakage or loosening.	Pulling strength: 5N Holding time: 10±1s Hold the capacitors to keep the axis vertical, bend it 90 degrees as shown below and bend back to the original position. This operation shall be done for 2~3s. and repeated for the following times. Bending force: 5N(weight: 0.51kg) Test time: 2 times
Solderability	Leads shall be covered by new solder more than 75% of its surface	Completely immerse both terminations in solder at 235± 5°C for 2±0.5s Solder : H63A Flux :Rosin Dipping :By 1.5~2.0mm form the root of lead
Resistance to Soldering Heat	Appearance No mechanical damage shall occur Capacitance Class I (NPO): Within 2.5% or ± 0.25 pF whichever is larger of initial value Class II X7R,X5R: $\leq \pm 10\%$ of initial value Y5V: $\leq \pm 20\%$ of initial value	- 250± 5℃ for 5±1s
	Q / Tanδ To satisfy the specified initial value	-
	Insulation To satisfy the specified initial value Resistance	-





RDC Series Specification & Test Condition

Item		Specification	Test Condition					
Temperature Cycle	Appearance Capacitance Q / Tano Insulation	No mechanical damage shall occur Class I (NPO): Within 2.5% or ±0.25pF whichever is larger of initial value Class II X7R,X5R: ≤ ±7.5% of initial value Y5V: ≤ ±20% of initial value see RDC specification data sheet To satisfy the specified initial	Class II capacitor shall be set for 48±4 hours at room temperature after one hour heat treatment at 150 +0/-10 °C before initial measurement. Capacitor shall be subjected to five cycles of the temperature cycle as following: Step Temp.(°C) Time(min) 1 Min Rated Temp.+0/-3 (-55) 30 2 25 3 Max Rated Temp.+3/-0 (125) 30 4 25 3					
	Resistance	value	Measure at room temperature after cooling for Class I : 24 \pm 2 Hours Class II : 48 \pm 4 Hours					
Humidity	Appearance Capacitance	No mechanical damage shall occur Class I (NPO): Within 5% or $\pm 0.5 pF$ whichever is larger of initial value Class II $X7R,X5R: \leq \pm 15\%$ of initial value $Y5V: \leq \pm 30\%$ of initial value	Class $\rm II$ capacitor shall be set for 48±4 hours at room temperature after one hour heat treatment at 150 +0/-10 $^{\circ}$ C before initial measurement. Temperature : 40± 2 $^{\circ}$ C Relative Humidity : 90 ~95%RH Test Time : 500 +12/-0 hr Measure at room temperature after cooling for Class I : 24 ± 2 Hours					
	Q / Tanδ	see RDC specification data sheet	Class II : 48 ± 4 Hours					
	Insulation Resistance	1,000M Ω or 50/C Ω whichever is smaller for rated voltage>10V and greater 10/C Ω for rated voltage \leq 1	0V					
High Temperature Load	Appearance	No mechanical damage shall occur	Class II capacitors applied DC testing voltage is applied for one hour at maximum operation					
(Life Test)	Capacitance	Class I (NPO): Within 5% or ± 0.5 pF whichever is larger of initial value Class II X7R,X5R : $\leq \pm 15\%$ of initial value Y5V : $\leq \pm 30\%$ of initial value	temperature ±3°C then shell be set for 48± 4 hours at room temperature and the initial measurement shall be conducted. Applied Voltage: V≤50Vdc 200%Rated Voltage V≤250Vdc 150%Rated Voltage V<1KVdc 120%Rated Voltage					
	Q / Tanδ	Class I (NPO): More Than 30pF : Q ≥ 350 30pF & Below: Q ≥ 275+2.5C Class II (X7R,X5R,Y5V): see RDC specification data sheet	V ≥ 1KV 100%Rated Voltage However: The rated voltage is 6.3V/10V,applied voltage of 100% Rated voltage. 150% Rated Voltage for C≥1.0uF and 200% Rated Voltage for C< 1.0uF.					
	Insulation Resistance	1,000M Ω or 50/C Ω whichever is smaller for rated voltage>10V and greater 10/C Ω for rated voltage \leq 10V	Temperature: max. operating temperature Test Time: 1000 +48/-0 Hr Current Applied: 50mA Max Measure at room temperature after cooling for Class I: 24 ± 2 Hours Class II: 48 ± 4 Hours					
Vibration	Appearance	No mechanical damage shall occur	Solder the capacitor on P.C. Board Vibrate the capacitor with amplitude of 1.5mm P					
	Capacitance	Within the specified tolerance	changing the frequencies from 10Hz to 55Hz and					
	Q / Tanō	To satisfy the specified initial value	 back to 10Hz in about 1min. Repeat this for 2 hours each in 3perpendicular directions. 					

