


# Mechanical Dimension & Schematic



Part No. : 5344-04-LFR

Rev.:

Sample No. : YT-25930

<b>Electrical Specification &amp; Test Report :</b>	<b>Remark :</b>
---	-----------------

Testing Item	Specification	Pin No.	Turn: 30Ts TYP.											
			1	2	3	4	5	6	7	8	9	10		
			INDUCTANCE @ 1KHz, 0.1Vrms WK3260B	30.0uH±25%	S – F									
DC RESISTANCE 502AC	< 60.0 mΩ	S – F												

**Materials list :**

Name		Description	UL No.
CORE		Iron Powder Core	N/A
WIRE		DD-NYU , 130°C , MW28C	E84081
		LUY, UEY, UEY-2# , 130°C , MW28-C	E174837
VARNISH		V1630FS , 130°C	E75225
SOLDER		Lead free	N/A

**Part No. :** 5344-04-LFR

**Rev.:**

**Sample No. :** YT-25930